

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866614

Luminaire Tested: PRLX-2004-M-940-25L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-M-940-25L-G-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 528.2 lumens
Efficiency: N/A
Efficacy: 24.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.14
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 21.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866614

CATALOG NUMBER: PRLX-2004-M-940-25L-G-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P866614

CATALOG NUMBER: PRLX-2004-M-940-25L-G-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56	65	60	56	64	59	55	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	46	43	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2644
5°	2649
10°	2639
15°	2614
20°	2565
25°	2509
30°	2394
35°	2092
40°	1700
45°	1268
50°	818
55°	419
60°	320
65°	271
70°	251
75°	221
80°	197
85°	201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1268 cd/sqm

TEST NUMBER: P866614

CATALOG NUMBER: PRLX-2004-M-940-25L-G-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.5	6.0
10°-20°	89.4	16.9
20°-30°	131.1	24.8
30°-40°	133.4	25.3
40°-50°	86.7	16.4
50°-60°	31.7	6.0
60°-70°	14.6	2.8
70°-80°	7.7	1.5
80°-90°	2.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	252.0	47.7
0°-40°	385.4	73.0
0°-60°	503.7	95.4
0°-90°	528.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	528.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	332	
5°	332	31
15°	317	89
25°	286	131
35°	215	133
45°	113	87
55°	30	32
65°	14	15
75°	7	8
85°	2	2
90°	0	

TEST NUMBER: P866614

CATALOG NUMBER: PRLX-2004-M-940-25L-G-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	332.4
2.5°	332.4
5°	331.7
7.5°	329.6
10°	326.7
12.5°	323.1
15°	317.4
17.5°	310.9
20°	303.0
22.5°	295.1
25°	285.8
27.5°	275.0
30°	260.6
32.5°	239.1
35°	215.4
37.5°	190.3
40°	163.7
42.5°	137.9
45°	112.7
47.5°	87.6
50°	66.1
52.5°	46.0
55°	30.2
57.5°	23.7
60°	20.1
62.5°	17.2
65°	14.4
67.5°	12.2
70°	10.8
72.5°	8.6
75°	7.2
77.5°	5.7
80°	4.3
82.5°	2.9
85°	2.2
87.5°	0.7
90°	0.0



TEST NUMBER: P866614
 CATALOG NUMBER: PRLX-2004-M-940-25L-G-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.46	5.71	4.82	6.02	6.34	4.46	5.71	4.82	6.02	6.34
	3H	5.64	6.75	6.02	7.08	7.44	5.64	6.75	6.02	7.08	7.44
	4H	6.08	7.11	6.49	7.46	7.85	6.08	7.11	6.49	7.46	7.85
	6H	6.41	7.35	6.83	7.73	8.12	6.41	7.35	6.83	7.73	8.12
	8H	6.50	7.40	6.93	7.79	8.19	6.50	7.40	6.93	7.79	8.19
	12H	6.58	7.43	7.01	7.81	8.24	6.58	7.43	7.01	7.81	8.24
4H	2H	4.81	5.84	5.21	6.19	6.57	4.81	5.84	5.21	6.19	6.57
	3H	6.22	7.06	6.63	7.46	7.87	6.22	7.06	6.63	7.46	7.87
	4H	6.78	7.53	7.22	7.95	8.40	6.78	7.53	7.22	7.95	8.40
	6H	7.23	7.87	7.69	8.32	8.79	7.23	7.87	7.69	8.32	8.79
	8H	7.36	7.96	7.83	8.41	8.88	7.36	7.96	7.83	8.41	8.88
	12H	7.47	8.00	7.96	8.49	8.96	7.47	8.00	7.96	8.49	8.96
8H	4H	6.96	7.56	7.43	8.00	8.48	6.96	7.56	7.43	8.00	8.48
	6H	7.51	8.00	8.01	8.49	8.98	7.51	8.00	8.01	8.49	8.98
	8H	7.70	8.14	8.22	8.65	9.15	7.70	8.14	8.22	8.65	9.15
	12H	7.90	8.29	8.41	8.78	9.36	7.90	8.29	8.41	8.78	9.36
12H	4H	6.95	7.48	7.44	7.96	8.44	6.95	7.48	7.44	7.96	8.44
	6H	7.52	7.96	8.05	8.48	8.97	7.52	7.96	8.05	8.48	8.97
	8H	7.76	8.15	8.28	8.65	9.22	7.76	8.15	8.28	8.65	9.22