

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219867

Luminaire Tested: **MRZ-1-REC-X-2-L40-97-WFL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14881)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-2-L40-97-WFL-UNV-X-STD-HEX
Description: MRZ INTEGRAL LED DOWNLIGHT
55 DEGREE WIDE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL2
Light Source: (1) 4000K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 329.4 lumens
Efficiency: N/A
Efficacy: 37.4 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.67
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219867

CATALOG NUMBER: MRZ-1-REC-X-2-L40-97-WFL-UNV-X-STD-HEX

Luminous Intensity Polar Plot





TEST NUMBER: P219867

CATALOG NUMBER: MRZ-1-REC-X-2-L40-97-WFL-UNV-X-STD-HEX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	81	78	84	80	78	83	79	77	76
6	92	84	78	75	90	83	78	74	82	77	74	80	76	73	79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62
10	78	69	64	61	77	69	64	60	68	63	60	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	318427
5°	301170
10°	266327
15°	215653
20°	164181
25°	121561
30°	78221
35°	41318
40°	17905
45°	6698
50°	2686
55°	1462
60°	888
65°	1051
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P219867

CATALOG NUMBER: MRZ-1-REC-X-2-L40-97-WFL-UNV-X-STD-HEX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.7	16.9
10°-20°	116.3	35.3
20°-30°	101.4	30.8
30°-40°	44.9	13.6
40°-50°	8.9	2.7
50°-60°	1.8	0.6
60°-70°	0.6	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	273.3	83.0
0°-40°	318.2	96.6
0°-60°	328.9	99.8
0°-90°	329.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	329.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	645	
5°	608	56
15°	422	116
25°	223	101
35°	69	45
45°	10	9
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P219867

CATALOG NUMBER: MRZ-1-REC-X-2-L40-97-WFL-UNV-X-STD-HEX

CANDELA DISTRIBUTION (FULL):

0°	
0°	645.4
2.5°	632.4
5°	608.1
7.5°	575.1
10°	531.6
12.5°	478.7
15°	422.2
17.5°	363.1
20°	312.7
22.5°	268.4
25°	223.3
27.5°	179.8
30°	137.3
32.5°	99.0
35°	68.6
37.5°	44.3
40°	27.8
42.5°	15.6
45°	9.6
47.5°	6.1
50°	3.5
52.5°	2.6
55°	1.7
57.5°	1.7
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)