

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701892

Luminaire Tested: 340-4C-10-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P701892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-7)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-10-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC
Description: FARALLON 4" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C
KIT.
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 651.9 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.65
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P701892

CATALOG NUMBER: 340-4C-10-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

Luminous Intensity Polar Plot



TEST NUMBER: P701892

CATALOG NUMBER: 340-4C-10-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	104	100	97	106	102	98	95	97	94	92		93	91	89		89	87	86	83
2	100	93	87	81	98	91	85	80	87	82	78		84	80	76		80	77	74	72
3	93	83	76	70	90	82	75	69	78	73	68		75	71	66		73	69	65	63
4	86	75	67	61	84	74	66	61	71	65	60		69	63	59		66	62	58	56
5	80	69	60	54	78	67	60	54	65	58	53		63	57	53		61	56	52	50
6	75	63	55	49	73	62	54	49	60	53	48		58	52	48		57	51	47	45
7	70	58	50	45	69	57	50	44	56	49	44		54	48	44		53	47	43	41
8	66	54	46	41	65	53	46	41	52	45	40		50	44	40		49	44	40	38
9	62	50	43	38	61	50	42	38	48	42	37		47	41	37		46	41	37	35
10	59	47	40	35	58	47	40	35	45	39	35		44	39	35		44	38	34	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75899
5°	64978
10°	46136
15°	28961
20°	20499
25°	15186
30°	12350
35°	10583
40°	9180
45°	7643
50°	6088
55°	4854
60°	3862
65°	3134
70°	2556
75°	2077
80°	1640
85°	1337

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7643 cd/sqm

TEST NUMBER: P701892

CATALOG NUMBER: 340-4C-10-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	8.8
10°-20°	99.2	15.2
20°-30°	99.4	15.2
30°-40°	102.5	15.7
40°-50°	96.5	14.8
50°-60°	74.0	11.3
60°-70°	52.7	8.1
70°-80°	36.0	5.5
80°-90°	22.5	3.5
90°-100°	10.7	1.6
100°-110°	1.0	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	256.1	39.3
0°-40°	358.6	55.0
0°-60°	529.1	81.2
0°-90°	640.3	98.2
90°-120°	11.6	1.8
90°-150°	11.6	1.8
90°-180°	12.0	1.8
0°-180°	651.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	654	
5°	641	58
15°	351	99
25°	213	99
35°	164	103
45°	126	96
55°	82	74
65°	53	53
75°	34	36
85°	20	18
90°	16	9
95°	10	7
105°	0	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P701892

CATALOG NUMBER: 340-4C-10-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

CANDELA DISTRIBUTION (FULL):

0°	
0°	654.4
1°	653.6
2°	648.1
3°	646.5
4°	644.9
5°	641.0
6°	634.6
7°	619.6
8°	592.8
9°	554.8
10°	509.0
11°	462.3
12°	423.6
13°	393.6
14°	370.7
15°	350.9
16°	331.9
17°	315.3
18°	298.7
19°	282.9
20°	268.7
21°	255.3
22°	243.4
23°	232.4
24°	222.9
25°	212.6
27.5°	193.6
30°	182.6
32.5°	172.3
35°	163.6
37.5°	154.9
40°	147.0
42.5°	136.7
45°	125.7
47.5°	113.8
50°	102.0
52.5°	91.7
55°	82.2
57.5°	73.5
60°	65.6
62.5°	58.5
65°	53.0
67.5°	47.4
70°	42.7
72.5°	37.9

TEST NUMBER: P701892

CATALOG NUMBER: 340-4C-10-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

CANDELA DISTRIBUTION (continued):

	0°
75°	34.0
77.5°	30.0
80°	26.1
82.5°	22.9
85°	20.5
87.5°	18.2
90°	15.8
92.5°	13.4
95°	9.5
97.5°	6.3
100°	4.0
102.5°	1.6
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)