

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701950

Luminaire Tested: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P701950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-3)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CC
Description: FARALLON 4" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1122.1 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.64
Luminous Opening: Circular (Dia: 0.34' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P701950

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

Luminous Intensity Polar Plot



TEST NUMBER: P701950

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81	78	75	73
5	91	82	76	72	89	82	76	72	80	75	71		78	74	70		76	73	70	68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72	68	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	57	56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62	57	54	53
10	71	62	56	52	70	61	55	52	60	55	52		59	55	51		59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	260324
5°	207926
10°	148617
15°	125994
20°	108011
25°	91424
30°	60079
35°	42873
40°	32749
45°	19257
50°	12703
55°	9241
60°	6031
65°	5434
70°	4612
75°	3316
80°	2471
85°	1597

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19257 cd/sqm

TEST NUMBER: P701950

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.8	13.5
10°-20°	291.8	26.0
20°-30°	315.2	28.1
30°-40°	194.7	17.3
40°-50°	97.5	8.7
50°-60°	40.9	3.6
60°-70°	19.3	1.7
70°-80°	8.5	0.8
80°-90°	1.8	0.2
90°-100°	0.2	0.0
100°-110°	0.5	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	758.8	67.6
0°-40°	953.5	85.0
0°-60°	1091.9	97.3
0°-90°	1121.5	99.9
90°-120°	0.6	0.1
90°-150°	0.6	0.1
90°-180°	1.0	0.1
0°-180°	1122.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2244	
5°	1786	152
15°	1049	292
25°	714	315
35°	303	195
45°	117	98
55°	46	41
65°	20	19
75°	7	8
85°	1	2
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P701950

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2244.5
1°	2233.4
2°	2170.3
3°	2066.5
4°	1931.8
5°	1785.9
6°	1640.1
7°	1507.9
8°	1402.8
9°	1323.7
10°	1261.9
11°	1208.8
12°	1163.0
13°	1123.5
14°	1087.6
15°	1049.3
16°	1011.0
17°	967.7
18°	928.2
19°	896.1
20°	875.1
21°	857.7
22°	835.5
23°	804.6
24°	762.6
25°	714.4
27.5°	574.7
30°	448.6
32.5°	362.1
35°	302.8
37.5°	259.5
40°	216.3
42.5°	161.9
45°	117.4
47.5°	89.0
50°	70.4
52.5°	58.1
55°	45.7
57.5°	32.1
60°	26.0
62.5°	22.2
65°	19.8
67.5°	16.1
70°	13.6
72.5°	9.9

TEST NUMBER: P701950

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

CANDELA DISTRIBUTION (continued):

	0°
75°	7.4
77.5°	6.2
80°	3.7
82.5°	2.5
85°	1.2
87.5°	1.2
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	1.2
102.5°	1.2
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)