

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865761

Luminaire Tested: PRLX-2004-S-927-20L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865761  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-24)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-S-927-20L-L-U-S-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, BELL WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 4  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 922.1 lumens  
Efficiency: N/A  
Efficacy: 42.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.02  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865761

CATALOG NUMBER: PRLX-2004-S-927-20L-L-U-S-X-X-BRSS-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865761

CATALOG NUMBER: PRLX-2004-S-927-20L-L-U-S-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99		99	98	96		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79	75	72	70
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74	70	67	65
6	84	74	68	63	83	74	67	63	72	67	62		71	66	62		69	65	62	60
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65	60	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	13355
5°	12960
10°	12395
15°	11962
20°	11518
25°	11167
30°	10782
35°	8598
40°	3336
45°	1329
50°	893
55°	864
60°	835
65°	741
70°	687
75°	706
80°	601
85°	599

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1329 cd/sqm

TEST NUMBER: P865761

CATALOG NUMBER: PRLX-2004-S-927-20L-L-U-S-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.2	8.0
10°-20°	199.3	21.6
20°-30°	285.7	31.0
30°-40°	246.8	26.8
40°-50°	54.2	5.9
50°-60°	27.2	2.9
60°-70°	19.6	2.1
70°-80°	11.6	1.3
80°-90°	3.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	559.2	60.6
0°-40°	806.0	87.4
0°-60°	887.4	96.2
0°-90°	922.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	922.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	819	
5°	792	74
15°	708	199
25°	620	286
35°	432	247
45°	58	54
55°	30	27
65°	19	20
75°	11	12
85°	3	3
90°	0	

TEST NUMBER: P865761

CATALOG NUMBER: PRLX-2004-S-927-20L-L-U-S-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	818.8
2.5°	814.0
5°	791.6
7.5°	769.2
10°	748.4
12.5°	729.2
15°	708.4
17.5°	686.0
20°	663.6
22.5°	641.3
25°	620.5
27.5°	599.7
30°	572.5
32.5°	522.9
35°	431.8
37.5°	286.2
40°	156.7
42.5°	92.8
45°	57.6
47.5°	40.0
50°	35.2
52.5°	33.6
55°	30.4
57.5°	27.2
60°	25.6
62.5°	22.4
65°	19.2
67.5°	17.6
70°	14.4
72.5°	12.8
75°	11.2
77.5°	9.6
80°	6.4
82.5°	4.8
85°	3.2
87.5°	1.6
90°	0.0

TEST NUMBER: P865761

CATALOG NUMBER: PRLX-2004-S-927-20L-L-U-S-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.26	7.32	6.62	7.63	7.95	6.26	7.32	6.62	7.63	7.95
	3H	7.89	8.83	8.27	9.16	9.53	7.89	8.83	8.27	9.16	9.53
	4H	8.56	9.44	8.97	9.79	10.18	8.56	9.44	8.97	9.79	10.18
	6H	9.10	9.90	9.51	10.27	10.67	9.10	9.90	9.51	10.27	10.67
	8H	9.24	10.00	9.68	10.39	10.80	9.24	10.00	9.68	10.39	10.80
	12H	9.35	10.07	9.78	10.45	10.88	9.35	10.07	9.78	10.45	10.88
4H	2H	6.73	7.60	7.13	7.95	8.34	6.73	7.60	7.13	7.95	8.34
	3H	8.56	9.28	8.98	9.69	10.09	8.56	9.28	8.98	9.69	10.09
	4H	9.39	10.03	9.83	10.45	10.90	9.39	10.03	9.83	10.45	10.90
	6H	10.05	10.60	10.52	11.05	11.52	10.05	10.60	10.52	11.05	11.52
	8H	10.24	10.75	10.72	11.20	11.68	10.24	10.75	10.72	11.20	11.68
	12H	10.39	10.83	10.88	11.32	11.80	10.39	10.83	10.88	11.32	11.80
8H	4H	9.66	10.17	10.14	10.62	11.10	9.66	10.17	10.14	10.62	11.10
	6H	10.44	10.85	10.95	11.35	11.83	10.44	10.85	10.95	11.35	11.83
	8H	10.71	11.07	11.24	11.59	12.09	10.71	11.07	11.24	11.59	12.09
	12H	10.95	11.27	11.47	11.76	12.34	10.95	11.27	11.47	11.76	12.34
12H	4H	9.66	10.11	10.15	10.60	11.07	9.66	10.11	10.15	10.60	11.07
	6H	10.47	10.84	11.00	11.36	11.85	10.47	10.84	11.00	11.36	11.85
	8H	10.80	11.12	11.32	11.62	12.19	10.80	11.12	11.32	11.62	12.19