

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865768

Luminaire Tested: PRLX-2004-S-927-25L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-26)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-927-25L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS,
BELL WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 5
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 969.9 lumens
Efficiency: N/A
Efficacy: 33.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 29.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865768

CATALOG NUMBER: PRLX-2004-S-927-25L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P865768

CATALOG NUMBER: PRLX-2004-S-927-25L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92	90	88	86
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82	78	76	74
5	91	83	77	72	90	82	76	72	80	75	72		78	74	71		77	73	70	69
6	87	78	71	67	85	77	71	67	75	70	66		74	69	66		72	68	65	64
7	82	73	66	62	81	72	66	62	71	65	62		69	65	61		68	64	61	59
8	78	68	62	58	77	67	62	58	66	61	57		65	61	57		64	60	57	55
9	74	64	58	54	73	63	58	54	63	57	53		62	57	53		61	56	53	52
10	70	60	54	50	69	60	54	50	59	54	50		58	53	50		57	53	50	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	15095
5°	14792
10°	14202
15°	13704
20°	13254
25°	12914
30°	12460
35°	9830
40°	3277
45°	738
50°	203
55°	171
60°	130
65°	154
70°	95
75°	126
80°	188
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 738 cd/sqm

TEST NUMBER: P865768

CATALOG NUMBER: PRLX-2004-S-927-25L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.7	8.7
10°-20°	228.7	23.6
20°-30°	330.0	34.0
30°-40°	278.8	28.7
40°-50°	36.3	3.7
50°-60°	5.4	0.6
60°-70°	3.7	0.4
70°-80°	2.1	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	643.3	66.3
0°-40°	922.2	95.1
0°-60°	963.8	99.4
0°-90°	969.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	969.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	926	
5°	904	85
15°	812	229
25°	718	330
35°	494	279
45°	32	36
55°	6	5
65°	4	4
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P865768

CATALOG NUMBER: PRLX-2004-S-927-25L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	925.5
2.5°	921.5
5°	903.5
7.5°	879.5
10°	857.5
12.5°	833.6
15°	811.6
17.5°	789.6
20°	763.6
22.5°	741.6
25°	717.6
27.5°	691.6
30°	661.6
32.5°	601.7
35°	493.7
37.5°	313.8
40°	153.9
42.5°	72.0
45°	32.0
47.5°	10.0
50°	8.0
52.5°	6.0
55°	6.0
57.5°	6.0
60°	4.0
62.5°	4.0
65°	4.0
67.5°	4.0
70°	2.0
72.5°	2.0
75°	2.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



TEST NUMBER: P865768

CATALOG NUMBER: PRLX-2004-S-927-25L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.39	0.00	0.00	0.00	0.00	0.39
	8H	0.00	0.00	0.00	0.00	0.38	0.00	0.00	0.00	0.00	0.38
	12H	0.00	0.00	0.00	0.00	0.29	0.00	0.00	0.00	0.00	0.29
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.27	0.76	0.00	0.00	0.00	0.27	0.76
	8H	0.00	0.00	0.00	0.27	0.77	0.00	0.00	0.00	0.27	0.77
	12H	0.00	0.00	0.00	0.15	0.73	0.00	0.00	0.00	0.15	0.73
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.27	0.77	0.00	0.00	0.00	0.27	0.77
	8H	0.00	0.00	0.00	0.24	0.82	0.00	0.00	0.00	0.24	0.82