

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702006

Luminaire Tested: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-3)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-CC
Description: FARALLON 4" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1446.9 lumens
Efficiency: N/A
Efficacy: 66.4 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.64
Luminous Opening: Circular (Dia: 0.34' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702006

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

Luminous Intensity Polar Plot



TEST NUMBER: P702006

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81	78	75	73
5	91	82	76	72	89	82	76	72	80	75	71		78	74	70		76	73	70	68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72	68	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	57	56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62	57	54	53
10	71	62	56	52	70	61	55	52	60	55	52		59	55	51		59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	335655
5°	268106
10°	191627
15°	162461
20°	139262
25°	117876
30°	77476
35°	55276
40°	42227
45°	24833
50°	16384
55°	11930
60°	7771
65°	6998
70°	5934
75°	4302
80°	3206
85°	2129

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24833 cd/sqm

TEST NUMBER: P702006

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.8	13.5
10°-20°	376.3	26.0
20°-30°	406.4	28.1
30°-40°	251.0	17.3
40°-50°	125.7	8.7
50°-60°	52.7	3.6
60°-70°	24.8	1.7
70°-80°	10.9	0.8
80°-90°	2.4	0.2
90°-100°	0.2	0.0
100°-110°	0.6	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	978.4	67.6
0°-40°	1229.5	85.0
0°-60°	1407.9	97.3
0°-90°	1446.1	99.9
90°-120°	0.9	0.1
90°-150°	0.9	0.1
90°-180°	1.0	0.1
0°-180°	1446.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2894	
5°	2303	196
15°	1353	376
25°	921	406
35°	390	251
45°	151	126
55°	59	53
65°	26	25
75°	10	11
85°	2	2
90°	0	0
95°	0	1
105°	0	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702006

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2894.0
1°	2879.7
2°	2798.4
3°	2664.5
4°	2490.8
5°	2302.8
6°	2114.7
7°	1944.2
8°	1808.8
9°	1706.8
10°	1627.1
11°	1558.6
12°	1499.6
13°	1448.6
14°	1402.4
15°	1353.0
16°	1303.6
17°	1247.8
18°	1196.8
19°	1155.4
20°	1128.3
21°	1106.0
22°	1077.3
23°	1037.4
24°	983.3
25°	921.1
27.5°	741.0
30°	578.5
32.5°	466.9
35°	390.4
37.5°	334.7
40°	278.9
42.5°	208.8
45°	151.4
47.5°	114.7
50°	90.8
52.5°	74.9
55°	59.0
57.5°	41.4
60°	33.5
62.5°	28.7
65°	25.5
67.5°	20.7
70°	17.5
72.5°	12.7

TEST NUMBER: P702006

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-CC

CANDELA DISTRIBUTION (continued):

	0°
75°	9.6
77.5°	8.0
80°	4.8
82.5°	3.2
85°	1.6
87.5°	1.6
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	1.6
102.5°	1.6
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)