

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865787

Luminaire Tested: PRLX-2004-S-930-10L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865787
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-23)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-930-10L-L-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, BELL WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 904.7 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.07
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865787

CATALOG NUMBER: PRLX-2004-S-930-10L-L-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot



TEST NUMBER: P865787

CATALOG NUMBER: PRLX-2004-S-930-10L-L-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60
5	83	72	64	58	81	70	63	58	68	62	57	67	61	57	65	60	56	54
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49
7	72	61	53	47	71	60	53	47	58	52	47	57	51	47	56	50	46	45
8	68	56	49	43	67	55	48	43	54	48	43	53	47	43	52	47	43	41
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38
10	60	49	42	37	59	48	41	37	47	41	37	46	41	36	45	40	36	35

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9204
5°	8970
10°	8687
15°	8492
20°	8309
25°	8165
30°	7991
35°	6847
40°	4011
45°	2989
50°	2720
55°	2630
60°	2508
65°	2435
70°	2351
75°	2288
80°	2188
85°	2096

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2989 cd/sqm

TEST NUMBER: P865787

CATALOG NUMBER: PRLX-2004-S-930-10L-L-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	5.7
10°-20°	141.7	15.7
20°-30°	208.9	23.1
30°-40°	202.7	22.4
40°-50°	104.4	11.5
50°-60°	82.6	9.1
60°-70°	62.5	6.9
70°-80°	38.1	4.2
80°-90°	12.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	402.2	44.5
0°-40°	604.8	66.9
0°-60°	791.8	87.5
0°-90°	904.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	904.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	564	
5°	548	52
15°	503	142
25°	454	209
35°	344	203
45°	130	104
55°	92	83
65°	63	62
75°	36	38
85°	11	12
90°	0	

TEST NUMBER: P865787

CATALOG NUMBER: PRLX-2004-S-930-10L-L-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	564.3
2.5°	560.8
5°	547.9
7.5°	535.8
10°	524.5
12.5°	513.3
15°	502.9
17.5°	490.8
20°	478.7
22.5°	466.6
25°	453.7
27.5°	439.9
30°	424.3
32.5°	395.8
35°	343.9
37.5°	263.6
40°	188.4
42.5°	151.2
45°	129.6
47.5°	114.9
50°	107.2
52.5°	100.2
55°	92.5
57.5°	84.7
60°	76.9
62.5°	70.0
65°	63.1
67.5°	56.2
70°	49.3
72.5°	42.3
75°	36.3
77.5°	29.4
80°	23.3
82.5°	17.3
85°	11.2
87.5°	5.2
90°	0.0



TEST NUMBER: P865787
 CATALOG NUMBER: PRLX-2004-S-930-10L-L-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.83	15.19	14.19	15.50	15.82	13.83	15.19	14.19	15.50	15.82
	3H	15.65	16.87	16.03	17.20	17.57	15.65	16.87	16.03	17.20	17.57
	4H	16.38	17.52	16.78	17.87	18.26	16.38	17.52	16.78	17.87	18.26
	6H	16.95	18.01	17.37	18.38	18.77	16.95	18.01	17.37	18.38	18.77
	8H	17.16	18.16	17.59	18.56	18.96	17.16	18.16	17.59	18.56	18.96
	12H	17.31	18.27	17.74	18.66	19.09	17.31	18.27	17.74	18.66	19.09
4H	2H	14.42	15.56	14.82	15.91	16.30	14.42	15.56	14.82	15.91	16.30
	3H	16.47	17.42	16.88	17.82	18.22	16.47	17.42	16.88	17.82	18.22
	4H	17.33	18.19	17.77	18.61	19.05	17.33	18.19	17.77	18.61	19.05
	6H	18.05	18.79	18.51	19.24	19.70	18.05	18.79	18.51	19.24	19.70
	8H	18.31	19.01	18.78	19.45	19.92	18.31	19.01	18.78	19.45	19.92
	12H	18.52	19.13	19.00	19.61	20.09	18.52	19.13	19.00	19.61	20.09
8H	4H	17.65	18.34	18.11	18.79	19.26	17.65	18.34	18.11	18.79	19.26
	6H	18.51	19.08	19.01	19.57	20.05	18.51	19.08	19.01	19.57	20.05
	8H	18.87	19.38	19.38	19.89	20.38	18.87	19.38	19.38	19.89	20.38
	12H	19.17	19.62	19.68	20.11	20.68	19.17	19.62	19.68	20.11	20.68
12H	4H	17.68	18.29	18.16	18.78	19.25	17.68	18.29	18.16	18.78	19.25
	6H	18.57	19.09	19.09	19.60	20.09	18.57	19.09	19.09	19.60	20.09
	8H	19.00	19.45	19.51	19.94	20.51	19.00	19.45	19.51	19.94	20.51