

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702009

Luminaire Tested: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-2)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-FF
Description: FARALLON 4" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1270.3 lumens
Efficiency: N/A
Efficacy: 58.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.73
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702009

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

Luminous Intensity Polar Plot



TEST NUMBER: P702009

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		100	100	100	97
1	109	105	102	98	107	103	99	96	98	95	93		94	92	90		90	88	86	84
2	102	95	89	85	99	93	88	83	89	85	81		86	82	79		82	80	77	75
3	95	87	80	75	93	85	79	74	82	77	72		79	75	71		76	73	69	67
4	89	80	73	67	87	78	72	67	76	70	65		73	68	64		71	67	63	61
5	84	74	66	61	82	73	66	61	70	64	60		68	63	59		66	62	58	56
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		62	58	54	52
7	75	64	57	52	73	63	56	52	62	56	51		60	55	51		59	54	50	49
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		55	51	47	45
9	68	57	50	45	66	56	50	45	55	49	45		54	48	44		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139922
5°	120995
10°	103855
15°	89044
20°	75739
25°	50879
30°	19404
35°	14329
40°	11147
45°	8816
50°	6941
55°	5645
60°	4786
65°	4335
70°	3909
75°	3604
80°	3306
85°	2909

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8816 cd/sqm

TEST NUMBER: P702009

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	8.8
10°-20°	302.6	23.8
20°-30°	299.3	23.6
30°-40°	140.4	11.1
40°-50°	112.1	8.8
50°-60°	86.5	6.8
60°-70°	72.7	5.7
70°-80°	62.4	4.9
80°-90°	48.7	3.8
90°-100°	28.1	2.2
100°-110°	5.1	0.4
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	714.4	56.2
0°-40°	854.8	67.3
0°-60°	1053.4	82.9
0°-90°	1237.1	97.4
90°-120°	33.2	2.6
90°-150°	33.2	2.6
90°-180°	33.0	2.6
0°-180°	1270.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1206	
5°	1194	112
15°	1079	303
25°	712	299
35°	222	140
45°	145	112
55°	96	87
65°	73	73
75°	59	62
85°	45	38
90°	37	20
95°	27	18
105°	3	5
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702009

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

CANDELA DISTRIBUTION (FULL):

0°	
0°	1206.4
2.5°	1203.2
5°	1193.6
7.5°	1174.5
10°	1145.8
12.5°	1113.9
15°	1078.9
17.5°	1039.0
20°	992.8
22.5°	922.7
25°	712.3
27.5°	409.6
30°	286.9
32.5°	247.0
35°	221.5
37.5°	200.8
40°	178.5
42.5°	161.0
45°	145.0
47.5°	129.1
50°	116.3
52.5°	105.2
55°	95.6
57.5°	87.6
60°	81.3
62.5°	76.5
65°	73.3
67.5°	70.1
70°	65.3
72.5°	62.2
75°	59.0
77.5°	55.8
80°	52.6
82.5°	47.8
85°	44.6
87.5°	41.4
90°	36.7
92.5°	33.5
95°	27.1
97.5°	17.5
100°	12.7
102.5°	8.0
105°	3.2
107.5°	1.6
110°	0.0

TEST NUMBER: P702009

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)