

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865806

Luminaire Tested: PRLX-2004-S-930-25L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865806  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-13)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-S-930-25L-G-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,  
BELL WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 5  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 448.0 lumens  
Efficiency: N/A  
Efficacy: 15.4 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.16  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 29.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865806

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865806

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72
4	91	81	74	69	89	80	74	68	78	72	68	76	71	67	74	69	66	64
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	78	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47
8	70	58	51	46	68	57	51	46	56	50	45	55	49	45	54	49	45	43
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4355
5°	4362
10°	4357
15°	4323
20°	4263
25°	4164
30°	3966
35°	3518
40°	2953
45°	2332
50°	1677
55°	1032
60°	607
65°	517
70°	463
75°	410
80°	385
85°	356

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2332 cd/sqm

TEST NUMBER: P865806

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.3	5.7
10°-20°	72.1	16.1
20°-30°	106.1	23.7
30°-40°	109.7	24.5
40°-50°	78.0	17.4
50°-60°	34.1	7.6
60°-70°	13.5	3.0
70°-80°	7.1	1.6
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.6	45.4
0°-40°	313.2	69.9
0°-60°	425.3	94.9
0°-90°	448.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	448.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	267	
5°	266	25
15°	256	72
25°	231	106
35°	177	110
45°	101	78
55°	36	34
65°	13	13
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P865806

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	267.0
2.5°	267.0
5°	266.4
7.5°	265.1
10°	263.1
12.5°	260.1
15°	256.0
17.5°	251.2
20°	245.6
22.5°	238.9
25°	231.4
27.5°	222.5
30°	210.6
32.5°	194.6
35°	176.7
37.5°	157.9
40°	138.7
42.5°	119.7
45°	101.1
47.5°	83.4
50°	66.1
52.5°	50.3
55°	36.3
57.5°	25.1
60°	18.6
62.5°	15.6
65°	13.4
67.5°	11.4
70°	9.7
72.5°	8.0
75°	6.5
77.5°	5.4
80°	4.1
82.5°	3.0
85°	1.9
87.5°	0.9
90°	0.0

TEST NUMBER: P865806

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.81	9.11	8.18	9.42	9.74	7.81	9.11	8.18	9.42	9.74
	3H	8.74	9.88	9.12	10.21	10.57	8.74	9.88	9.12	10.21	10.57
	4H	9.09	10.15	9.49	10.50	10.89	9.09	10.15	9.49	10.50	10.89
	6H	9.38	10.36	9.80	10.73	11.12	9.38	10.36	9.80	10.73	11.12
	8H	9.48	10.40	9.91	10.80	11.20	9.48	10.40	9.91	10.80	11.20
	12H	9.54	10.43	9.98	10.81	11.24	9.54	10.43	9.98	10.81	11.24
4H	2H	8.05	9.12	8.46	9.47	9.85	8.05	9.12	8.46	9.47	9.85
	3H	9.20	10.06	9.61	10.47	10.87	9.20	10.06	9.61	10.47	10.87
	4H	9.67	10.44	10.10	10.86	11.30	9.67	10.44	10.10	10.86	11.30
	6H	10.09	10.75	10.55	11.20	11.67	10.09	10.75	10.55	11.20	11.67
	8H	10.23	10.85	10.70	11.30	11.77	10.23	10.85	10.70	11.30	11.77
	12H	10.33	10.88	10.82	11.37	11.84	10.33	10.88	10.82	11.37	11.84
8H	4H	9.81	10.43	10.28	10.88	11.35	9.81	10.43	10.28	10.88	11.35
	6H	10.34	10.85	10.84	11.35	11.83	10.34	10.85	10.84	11.35	11.83
	8H	10.55	11.01	11.07	11.52	12.02	10.55	11.01	11.07	11.52	12.02
	12H	10.73	11.14	11.25	11.63	12.20	10.73	11.14	11.25	11.63	12.20
12H	4H	9.81	10.36	10.29	10.84	11.31	9.81	10.36	10.29	10.84	11.31
	6H	10.36	10.82	10.88	11.33	11.82	10.36	10.82	10.88	11.33	11.82
	8H	10.62	11.03	11.14	11.52	12.09	10.62	11.03	11.14	11.52	12.09