

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865807

Luminaire Tested: PRLX-2004-S-930-25L-G-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865807
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-930-25L-G-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,
BELL WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 5
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1292.7 lumens
Efficiency: N/A
Efficacy: 44.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.21
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 29.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865807

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P865807

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86
2	101	94	88	83	99	92	86	82	88	84	80	85	81	78	82	79	76	74
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	50	46	44
7	69	56	48	43	67	56	48	42	54	47	42	53	47	42	52	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	43	38	48	42	38	36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	35	44	39	34	33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9902
5°	9904
10°	9876
15°	9849
20°	9788
25°	9525
30°	9074
35°	8345
40°	7497
45°	6678
50°	5811
55°	5039
60°	4368
65°	4002
70°	3810
75°	3542
80°	3447
85°	3237

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6678 cd/sqm

TEST NUMBER: P865807

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	4.4
10°-20°	164.3	12.7
20°-30°	242.9	18.8
30°-40°	261.0	20.2
40°-50°	223.5	17.3
50°-60°	159.6	12.3
60°-70°	103.9	8.0
70°-80°	61.0	4.7
80°-90°	19.1	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	464.7	35.9
0°-40°	725.7	56.1
0°-60°	1108.8	85.8
0°-90°	1292.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1292.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	607	
5°	605	58
15°	583	164
25°	529	243
35°	419	261
45°	290	224
55°	177	160
65°	104	104
75°	56	61
85°	17	19
90°	0	

TEST NUMBER: P865807

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	607.1
2.5°	607.1
5°	604.9
7.5°	602.7
10°	596.3
12.5°	589.8
15°	583.3
17.5°	572.5
20°	563.9
22.5°	548.7
25°	529.3
27.5°	507.7
30°	481.8
32.5°	451.5
35°	419.1
37.5°	384.5
40°	352.1
42.5°	321.9
45°	289.5
47.5°	259.2
50°	229.0
52.5°	203.1
55°	177.2
57.5°	153.4
60°	133.9
62.5°	118.8
65°	103.7
67.5°	90.7
70°	79.9
72.5°	69.1
75°	56.2
77.5°	47.5
80°	36.7
82.5°	25.9
85°	17.3
87.5°	8.6
90°	0.0



TEST NUMBER: P865807
 CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.53	18.02	16.89	18.34	18.65	16.53	18.02	16.89	18.34	18.65
	3H	18.06	19.40	18.44	19.73	20.09	18.06	19.40	18.44	19.73	20.09
	4H	18.68	19.93	19.08	20.28	20.66	18.68	19.93	19.08	20.28	20.66
	6H	19.19	20.36	19.61	20.72	21.11	19.19	20.36	19.61	20.72	21.11
	8H	19.37	20.47	19.79	20.86	21.26	19.37	20.47	19.79	20.86	21.26
	12H	19.49	20.55	19.92	20.93	21.36	19.49	20.55	19.92	20.93	21.36
4H	2H	17.03	18.28	17.43	18.63	19.01	17.03	18.28	17.43	18.63	19.01
	3H	18.82	19.86	19.23	20.26	20.66	18.82	19.86	19.23	20.26	20.66
	4H	19.57	20.51	20.00	20.92	21.36	19.57	20.51	20.00	20.92	21.36
	6H	20.23	21.05	20.69	21.49	21.95	20.23	21.05	20.69	21.49	21.95
	8H	20.45	21.22	20.92	21.66	22.13	20.45	21.22	20.92	21.66	22.13
	12H	20.63	21.31	21.11	21.79	22.26	20.63	21.31	21.11	21.79	22.26
8H	4H	19.86	20.62	20.32	21.07	21.53	19.86	20.62	20.32	21.07	21.53
	6H	20.65	21.29	21.15	21.78	22.26	20.65	21.29	21.15	21.78	22.26
	8H	20.96	21.53	21.47	22.04	22.53	20.96	21.53	21.47	22.04	22.53
	12H	21.22	21.73	21.73	22.22	22.78	21.22	21.73	21.73	22.22	22.78
12H	4H	19.89	20.57	20.37	21.05	21.52	19.89	20.57	20.37	21.05	21.52
	6H	20.71	21.28	21.23	21.79	22.28	20.71	21.28	21.23	21.79	22.28
	8H	21.08	21.58	21.59	22.07	22.64	21.08	21.58	21.59	22.07	22.64