

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702065

Luminaire Tested: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-FF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702065
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-2)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-FF
Description: FARALLON 4" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1596.3 lumens
Efficiency: N/A
Efficacy: 50.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.73
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702065

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-FF

Luminous Intensity Polar Plot



TEST NUMBER: P702065

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-FF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		100	100	100	97
1	109	105	102	98	107	103	99	96	98	95	93		94	92	90		90	88	86	84
2	102	95	89	85	99	93	88	83	89	85	81		86	82	79		82	80	77	75
3	95	87	80	75	93	85	79	74	82	77	72		79	75	71		76	73	69	67
4	89	80	73	67	87	78	72	67	76	70	65		73	68	64		71	67	63	61
5	84	74	66	61	82	73	66	61	70	64	60		68	63	59		66	62	58	56
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		62	58	54	52
7	75	64	57	52	73	63	56	52	62	56	51		60	55	51		59	54	50	49
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		55	51	47	45
9	68	57	50	45	66	56	50	45	55	49	45		54	48	44		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	175830
5°	152055
10°	130513
15°	111897
20°	95185
25°	63943
30°	24382
35°	18010
40°	14007
45°	11078
50°	8726
55°	7098
60°	6010
65°	5447
70°	4915
75°	4527
80°	4154
85°	3659

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11078 cd/sqm

TEST NUMBER: P702065

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-FF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.3	8.8
10°-20°	380.3	23.8
20°-30°	376.2	23.6
30°-40°	176.4	11.1
40°-50°	140.9	8.8
50°-60°	108.8	6.8
60°-70°	91.3	5.7
70°-80°	78.3	4.9
80°-90°	61.2	3.8
90°-100°	35.3	2.2
100°-110°	6.4	0.4
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	897.7	56.2
0°-40°	1074.2	67.3
0°-60°	1323.8	82.9
0°-90°	1554.7	97.4
90°-120°	41.7	2.6
90°-150°	41.7	2.6
90°-180°	42.0	2.6
0°-180°	1596.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1516	
5°	1500	141
15°	1356	380
25°	895	376
35°	278	176
45°	182	141
55°	120	109
65°	92	91
75°	74	78
85°	56	48
90°	46	26
95°	34	23
105°	4	6
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702065

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-FF

CANDELA DISTRIBUTION (FULL):

0°	
0°	1516.0
2.5°	1512.0
5°	1500.0
7.5°	1476.0
10°	1439.9
12.5°	1399.9
15°	1355.8
17.5°	1305.7
20°	1247.7
22.5°	1159.5
25°	895.2
27.5°	514.7
30°	360.5
32.5°	310.4
35°	278.4
37.5°	252.3
40°	224.3
42.5°	202.3
45°	182.2
47.5°	162.2
50°	146.2
52.5°	132.2
55°	120.2
57.5°	110.1
60°	102.1
62.5°	96.1
65°	92.1
67.5°	88.1
70°	82.1
72.5°	78.1
75°	74.1
77.5°	70.1
80°	66.1
82.5°	60.1
85°	56.1
87.5°	52.1
90°	46.1
92.5°	42.1
95°	34.0
97.5°	22.0
100°	16.0
102.5°	10.0
105°	4.0
107.5°	2.0
110°	0.0

TEST NUMBER: P702065

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-FF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)