

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865818

Luminaire Tested: PRLX-2004-S-935-05L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-25)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-935-05L-L-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 259.8 lumens
Efficiency: N/A
Efficacy: 41.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.02
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 6.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865818

CATALOG NUMBER: PRLX-2004-S-935-05L-L-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P865818

CATALOG NUMBER: PRLX-2004-S-935-05L-L-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71
5	89	80	74	69	87	79	73	68	77	72	68	75	71	67	74	70	67	65
6	84	74	68	63	83	74	67	63	72	67	63	71	66	62	69	65	62	60
7	80	70	63	58	78	69	63	58	67	62	58	66	61	58	65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	55	50	70	60	54	50	59	54	50	59	53	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	47	54	50	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3756
5°	3674
10°	3521
15°	3384
20°	3267
25°	3158
30°	3032
35°	2359
40°	973
45°	385
50°	254
55°	245
60°	222
65°	208
70°	196
75°	202
80°	169
85°	168

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 385 cd/sqm

TEST NUMBER: P865818

CATALOG NUMBER: PRLX-2004-S-935-05L-L-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.0	8.1
10°-20°	56.5	21.7
20°-30°	80.8	31.1
30°-40°	68.7	26.4
40°-50°	15.6	6.0
50°-60°	7.5	2.9
60°-70°	5.5	2.1
70°-80°	3.2	1.2
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	158.3	60.9
0°-40°	227.0	87.4
0°-60°	250.1	96.3
0°-90°	259.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	259.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	230	
5°	224	21
15°	200	56
25°	176	81
35°	118	69
45°	17	16
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P865818

CATALOG NUMBER: PRLX-2004-S-935-05L-L-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	230.3
2.5°	229.4
5°	224.4
7.5°	218.5
10°	212.6
12.5°	206.7
15°	200.4
17.5°	194.5
20°	188.2
22.5°	181.9
25°	175.5
27.5°	169.2
30°	161.0
32.5°	145.2
35°	118.5
37.5°	79.6
40°	45.7
42.5°	26.7
45°	16.7
47.5°	11.3
50°	10.0
52.5°	9.0
55°	8.6
57.5°	7.7
60°	6.8
62.5°	6.3
65°	5.4
67.5°	5.0
70°	4.1
72.5°	3.6
75°	3.2
77.5°	2.3
80°	1.8
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0



TEST NUMBER: P865818
 CATALOG NUMBER: PRLX-2004-S-935-05L-L-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.86	2.92	2.22	3.24	3.55	1.86	2.92	2.22	3.24	3.55
	3H	3.51	4.46	3.90	4.79	5.16	3.51	4.46	3.90	4.79	5.16
	4H	4.19	5.07	4.60	5.42	5.81	4.19	5.07	4.60	5.42	5.81
	6H	4.61	5.41	5.02	5.78	6.18	4.61	5.41	5.02	5.78	6.18
	8H	4.77	5.52	5.20	5.91	6.32	4.77	5.52	5.20	5.91	6.32
	12H	4.88	5.60	5.31	5.98	6.41	4.88	5.60	5.31	5.98	6.41
4H	2H	2.33	3.20	2.73	3.55	3.94	2.33	3.20	2.73	3.55	3.94
	3H	4.18	4.90	4.60	5.31	5.71	4.18	4.90	4.60	5.31	5.71
	4H	5.01	5.65	5.45	6.08	6.53	5.01	5.65	5.45	6.08	6.53
	6H	5.55	6.10	6.02	6.55	7.02	5.55	6.10	6.02	6.55	7.02
	8H	5.75	6.27	6.23	6.72	7.19	5.75	6.27	6.23	6.72	7.19
	12H	5.91	6.36	6.41	6.85	7.32	5.91	6.36	6.41	6.85	7.32
8H	4H	5.24	5.75	5.72	6.20	6.68	5.24	5.75	5.72	6.20	6.68
	6H	5.90	6.31	6.41	6.81	7.30	5.90	6.31	6.41	6.81	7.30
	8H	6.20	6.57	6.73	7.09	7.58	6.20	6.57	6.73	7.09	7.58
	12H	6.46	6.78	6.98	7.28	7.85	6.46	6.78	6.98	7.28	7.85
12H	4H	5.24	5.68	5.73	6.17	6.65	5.24	5.68	5.73	6.17	6.65
	6H	5.94	6.31	6.47	6.83	7.32	5.94	6.31	6.47	6.83	7.32
	8H	6.30	6.62	6.82	7.12	7.70	6.30	6.62	6.82	7.12	7.70