

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865826

Luminaire Tested: PRLX-2004-S-935-10L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-25)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-935-10L-L-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 519.5 lumens
Efficiency: N/A
Efficacy: 49.5 lumens/watt
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.02
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865826

CATALOG NUMBER: PRLX-2004-S-935-10L-L-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P865826

CATALOG NUMBER: PRLX-2004-S-935-10L-L-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71
5	89	80	74	69	87	79	73	68	77	72	68	75	71	67	74	70	67	65
6	84	74	68	63	83	74	67	63	72	67	63	71	66	62	69	65	62	60
7	80	70	63	58	78	69	63	58	67	62	58	66	61	58	65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	55	50	70	60	54	50	59	54	50	59	53	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	47	54	50	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7511
5°	7348
10°	7042
15°	6768
20°	6533
25°	6318
30°	6066
35°	4719
40°	1946
45°	773
50°	505
55°	489
60°	444
65°	421
70°	386
75°	397
80°	338
85°	337

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 773 cd/sqm

TEST NUMBER: P865826

CATALOG NUMBER: PRLX-2004-S-935-10L-L-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.1	8.1
10°-20°	113.0	21.7
20°-30°	161.6	31.1
30°-40°	137.3	26.4
40°-50°	31.3	6.0
50°-60°	15.1	2.9
60°-70°	11.0	2.1
70°-80°	6.3	1.2
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	316.6	60.9
0°-40°	454.0	87.4
0°-60°	500.3	96.3
0°-90°	519.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	519.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	460	
5°	449	42
15°	401	113
25°	351	162
35°	237	137
45°	34	31
55°	17	15
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P865826

CATALOG NUMBER: PRLX-2004-S-935-10L-L-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	460.5
2.5°	458.7
5°	448.8
7.5°	437.0
10°	425.2
12.5°	413.5
15°	400.8
17.5°	389.1
20°	376.4
22.5°	363.7
25°	351.1
27.5°	338.4
30°	322.1
32.5°	290.4
35°	237.0
37.5°	159.2
40°	91.4
42.5°	53.4
45°	33.5
47.5°	22.6
50°	19.9
52.5°	18.1
55°	17.2
57.5°	15.4
60°	13.6
62.5°	12.7
65°	10.9
67.5°	10.0
70°	8.1
72.5°	7.2
75°	6.3
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0



TEST NUMBER: P865826
 CATALOG NUMBER: PRLX-2004-S-935-10L-L-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.27	5.33	4.63	5.64	5.96	4.27	5.33	4.63	5.64	5.96
	3H	5.91	6.85	6.29	7.18	7.55	5.91	6.85	6.29	7.18	7.55
	4H	6.58	7.45	6.98	7.81	8.19	6.58	7.45	6.98	7.81	8.19
	6H	6.98	7.78	7.40	8.16	8.55	6.98	7.78	7.40	8.16	8.55
	8H	7.13	7.89	7.57	8.28	8.69	7.13	7.89	7.57	8.28	8.69
	12H	7.24	7.96	7.68	8.35	8.78	7.24	7.96	7.68	8.35	8.78
4H	2H	4.75	5.62	5.15	5.97	6.36	4.75	5.62	5.15	5.97	6.36
	3H	6.58	7.30	7.00	7.71	8.11	6.58	7.30	7.00	7.71	8.11
	4H	7.39	8.03	7.83	8.46	8.91	7.39	8.03	7.83	8.46	8.91
	6H	7.92	8.47	8.39	8.92	9.39	7.92	8.47	8.39	8.92	9.39
	8H	8.11	8.63	8.59	9.08	9.55	8.11	8.63	8.59	9.08	9.55
	12H	8.27	8.72	8.76	9.20	9.68	8.27	8.72	8.76	9.20	9.68
8H	4H	7.61	8.13	8.09	8.57	9.05	7.61	8.13	8.09	8.57	9.05
	6H	8.27	8.68	8.78	9.18	9.66	8.27	8.68	8.78	9.18	9.66
	8H	8.55	8.92	9.08	9.44	9.93	8.55	8.92	9.08	9.44	9.93
	12H	8.81	9.12	9.33	9.62	10.20	8.81	9.12	9.33	9.62	10.20
12H	4H	7.61	8.06	8.10	8.54	9.02	7.61	8.06	8.10	8.54	9.02
	6H	8.30	8.67	8.83	9.19	9.68	8.30	8.67	8.83	9.19	9.68
	8H	8.65	8.97	9.17	9.46	10.04	8.65	8.97	9.17	9.46	10.04