

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702125

Luminaire Tested: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-CC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702125  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-CC  
Description: FARALLON 4" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.  
Light Source: 2700K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1980.3 lumens  
Efficiency: N/A  
Efficacy: 62.7 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.64  
Luminous Opening: Circular (Dia: 0.34' x H: 0')  
CIE Type: Direct

Input Watts (W): 31.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702125

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-CC

### Luminous Intensity Polar Plot



TEST NUMBER: P702125

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-CC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81	78	75	73
5	91	82	76	72	89	82	76	72	80	75	71		78	74	70		76	73	70	68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72	68	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	57	56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62	57	54	53
10	71	62	56	52	70	61	55	52	60	55	52		59	55	51		59	54	51	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	459398
5°	366940
10°	262267
15°	222354
20°	190596
25°	161336
30°	106029
35°	75665
40°	57791
45°	33986
50°	22428
55°	16318
60°	10624
65°	9578
70°	8139
75°	5870
80°	4341
85°	2928

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 33986 cd/sqm

TEST NUMBER: P702125

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-CC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	268.0	13.5
10°-20°	515.0	26.0
20°-30°	556.2	28.1
30°-40°	343.6	17.3
40°-50°	172.1	8.7
50°-60°	72.2	3.6
60°-70°	34.0	1.7
70°-80°	14.9	0.8
80°-90°	3.3	0.2
90°-100°	0.3	0.0
100°-110°	0.9	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1339.1	67.6
0°-40°	1682.7	85.0
0°-60°	1926.9	97.3
0°-90°	1979.1	99.9
90°-120°	1.2	0.1
90°-150°	1.2	0.1
90°-180°	1.0	0.1
0°-180°	1980.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3961	
5°	3152	268
15°	1852	515
25°	1261	556
35°	534	344
45°	207	172
55°	81	72
65°	35	34
75°	13	15
85°	2	3
90°	0	0
95°	0	1
105°	0	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702125

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-CC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3960.9
1°	3941.2
2°	3830.0
3°	3646.8
4°	3409.1
5°	3151.7
6°	2894.3
7°	2660.9
8°	2475.5
9°	2336.0
10°	2226.9
11°	2133.1
12°	2052.4
13°	1982.6
14°	1919.4
15°	1851.8
16°	1784.1
17°	1707.8
18°	1638.0
19°	1581.3
20°	1544.2
21°	1513.7
22°	1474.4
23°	1419.9
24°	1345.7
25°	1260.7
27.5°	1014.2
30°	791.7
32.5°	639.1
35°	534.4
37.5°	458.0
40°	381.7
42.5°	285.7
45°	207.2
47.5°	157.0
50°	124.3
52.5°	102.5
55°	80.7
57.5°	56.7
60°	45.8
62.5°	39.3
65°	34.9
67.5°	28.4
70°	24.0
72.5°	17.4

TEST NUMBER: P702125

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-CC

**CANDELA DISTRIBUTION (continued):**

	0°
75°	13.1
77.5°	10.9
80°	6.5
82.5°	4.4
85°	2.2
87.5°	2.2
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	2.2
102.5°	2.2
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)