

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702098

Luminaire Tested: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-CF

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702098  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-CF  
Description: FARALLON 4" LED GLASS DOWNLIGHT. CYLINDRICAL FROSTED GLASS KIT.  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1942.2 lumens  
Efficiency: N/A  
Efficacy: 61.5 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.45  
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702098

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-CF

### Luminous Intensity Polar Plot



TEST NUMBER: P702098

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-CF

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	98	106	103	99	96	98	95	92		94	91	89		90	88	86	84
2	101	94	88	83	98	92	86	82	88	83	80		85	81	77		81	78	75	73
3	94	85	78	72	91	83	76	71	80	74	70		77	72	68		74	70	67	65
4	87	77	70	64	85	76	69	63	73	67	62		71	65	61		68	64	60	58
5	82	71	63	57	80	70	62	57	67	61	56		65	60	55		63	59	55	53
6	77	65	58	52	75	64	57	52	62	56	51		61	55	51		59	54	50	48
7	72	61	53	48	71	60	53	48	58	52	47		57	51	47		55	50	46	45
8	69	57	49	44	67	56	49	44	55	48	44		53	48	43		52	47	43	41
9	65	53	46	41	64	53	46	41	52	45	41		50	45	41		49	44	40	39
10	62	50	43	39	61	50	43	39	49	43	39		48	42	38		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	435111
5°	287172
10°	159735
15°	118301
20°	57102
25°	38879
30°	30219
35°	26995
40°	24217
45°	20965
50°	17326
55°	14065
60°	11350
65°	8989
70°	7059
75°	5681
80°	4563
85°	3698

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20965 cd/sqm

TEST NUMBER: P702098

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-CF

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	231.8	11.9
10°-20°	365.7	18.8
20°-30°	254.2	13.1
30°-40°	260.4	13.4
40°-50°	264.0	13.6
50°-60°	214.1	11.0
60°-70°	151.2	7.8
70°-80°	98.8	5.1
80°-90°	62.1	3.2
90°-100°	33.5	1.7
100°-110°	6.4	0.3
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	851.6	43.8
0°-40°	1112.1	57.3
0°-60°	1590.2	81.9
0°-90°	1902.3	97.9
90°-120°	39.8	2.1
90°-150°	39.8	2.1
90°-180°	40.0	2.1
0°-180°	1942.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3752	
5°	2833	232
15°	1433	366
25°	544	254
35°	417	260
45°	345	264
55°	238	214
65°	152	151
75°	93	99
85°	57	49
90°	43	24
95°	32	22
105°	4	6
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702098

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-CF

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3751.5
1°	3737.9
2°	3644.9
3°	3431.7
4°	3143.6
5°	2832.9
6°	2519.9
7°	2238.6
8°	2036.8
9°	1878.0
10°	1762.3
11°	1678.4
12°	1610.4
13°	1553.7
14°	1499.2
15°	1433.4
16°	1329.1
17°	1186.2
18°	1022.9
19°	866.4
20°	748.5
21°	675.9
22°	628.3
23°	598.8
24°	571.6
25°	544.3
27.5°	485.4
30°	446.8
32.5°	424.1
35°	417.3
37.5°	403.7
40°	387.8
42.5°	367.4
45°	344.8
47.5°	317.5
50°	290.3
52.5°	263.1
55°	238.2
57.5°	215.5
60°	192.8
62.5°	170.1
65°	152.0
67.5°	133.8
70°	117.9
72.5°	104.3

TEST NUMBER: P702098

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-CF

**CANDELA DISTRIBUTION (continued):**

	0°
75°	93.0
77.5°	81.7
80°	72.6
82.5°	63.5
85°	56.7
87.5°	49.9
90°	43.1
92.5°	38.6
95°	31.8
97.5°	22.7
100°	15.9
102.5°	9.1
105°	4.5
107.5°	2.3
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)