

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865859

Luminaire Tested: PRLX-2004-S-940-05L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865859
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-23)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-940-05L-L-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, BELL WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 489.9 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.07
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 6.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865859

CATALOG NUMBER: PRLX-2004-S-940-05L-L-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P865859

CATALOG NUMBER: PRLX-2004-S-940-05L-L-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60
5	83	72	64	58	81	70	63	58	68	62	57	67	61	57	65	60	56	54
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49
7	72	61	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45
8	68	56	49	43	67	55	48	43	54	48	43	53	47	43	52	47	43	41
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38
10	60	49	42	37	59	48	41	37	47	41	37	46	41	36	45	40	36	35

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4983
5°	4856
10°	4704
15°	4598
20°	4499
25°	4420
30°	4326
35°	3707
40°	2172
45°	1619
50°	1472
55°	1425
60°	1357
65°	1320
70°	1273
75°	1241
80°	1183
85°	1142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1619 cd/sqm

TEST NUMBER: P865859

CATALOG NUMBER: PRLX-2004-S-940-05L-L-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.9	5.7
10°-20°	76.7	15.7
20°-30°	113.1	23.1
30°-40°	109.7	22.4
40°-50°	56.5	11.5
50°-60°	44.7	9.1
60°-70°	33.8	6.9
70°-80°	20.6	4.2
80°-90°	6.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	217.8	44.5
0°-40°	327.5	66.8
0°-60°	428.7	87.5
0°-90°	489.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	489.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	306	
5°	297	28
15°	272	77
25°	246	113
35°	186	110
45°	70	57
55°	50	45
65°	34	34
75°	20	21
85°	6	7
90°	0	

TEST NUMBER: P865859

CATALOG NUMBER: PRLX-2004-S-940-05L-L-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	305.5
2.5°	303.7
5°	296.6
7.5°	290.1
10°	284.0
12.5°	277.9
15°	272.3
17.5°	265.8
20°	259.2
22.5°	252.7
25°	245.6
27.5°	238.1
30°	229.7
32.5°	214.3
35°	186.2
37.5°	142.7
40°	102.0
42.5°	81.9
45°	70.2
47.5°	62.2
50°	58.0
52.5°	54.3
55°	50.1
57.5°	45.9
60°	41.6
62.5°	37.9
65°	34.2
67.5°	30.4
70°	26.7
72.5°	22.9
75°	19.7
77.5°	15.9
80°	12.6
82.5°	9.4
85°	6.1
87.5°	2.8
90°	0.0



TEST NUMBER: P865859
 CATALOG NUMBER: PRLX-2004-S-940-05L-L-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.70	13.06	12.06	13.38	13.69	11.70	13.06	12.06	13.38	13.69
	3H	13.52	14.74	13.90	15.07	15.43	13.52	14.74	13.90	15.07	15.43
	4H	14.25	15.40	14.65	15.75	16.13	14.25	15.40	14.65	15.75	16.13
	6H	14.82	15.88	15.24	16.25	16.64	14.82	15.88	15.24	16.25	16.64
	8H	15.03	16.03	15.46	16.43	16.83	15.03	16.03	15.46	16.43	16.83
	12H	15.19	16.14	15.62	16.53	16.96	15.19	16.14	15.62	16.53	16.96
4H	2H	12.29	13.44	12.69	13.79	14.17	12.29	13.44	12.69	13.79	14.17
	3H	14.34	15.29	14.75	15.69	16.09	14.34	15.29	14.75	15.69	16.09
	4H	15.21	16.06	15.64	16.48	16.92	15.21	16.06	15.64	16.48	16.92
	6H	15.92	16.66	16.38	17.11	17.57	15.92	16.66	16.38	17.11	17.57
	8H	16.18	16.88	16.65	17.32	17.79	16.18	16.88	16.65	17.32	17.79
	12H	16.39	17.01	16.87	17.49	17.96	16.39	17.01	16.87	17.49	17.96
8H	4H	15.52	16.21	15.99	16.66	17.13	15.52	16.21	15.99	16.66	17.13
	6H	16.38	16.95	16.88	17.44	17.92	16.38	16.95	16.88	17.44	17.92
	8H	16.74	17.25	17.26	17.76	18.25	16.74	17.25	17.26	17.76	18.25
	12H	17.04	17.49	17.56	17.99	18.55	17.04	17.49	17.56	17.99	18.55
12H	4H	15.55	16.17	16.03	16.65	17.12	15.55	16.17	16.03	16.65	17.12
	6H	16.44	16.96	16.96	17.47	17.96	16.44	16.96	16.96	17.47	17.96
	8H	16.87	17.32	17.39	17.81	18.38	16.87	17.32	17.39	17.81	18.38