

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865867

Luminaire Tested: PRLX-2004-S-940-10L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-23)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-940-10L-L-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, BELL WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 979.7 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.07
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865867

CATALOG NUMBER: PRLX-2004-S-940-10L-L-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P865867

CATALOG NUMBER: PRLX-2004-S-940-10L-L-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60
5	83	72	64	58	81	70	63	58	68	62	57	67	61	57	65	60	56	54
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49
7	72	61	53	47	71	60	53	47	58	52	47	57	51	47	56	50	46	45
8	68	56	49	43	67	55	48	43	54	48	43	53	47	43	52	47	43	41
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38
10	60	49	42	37	59	48	41	37	47	41	37	46	41	36	45	40	36	35

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9965
5°	9714
10°	9407
15°	9196
20°	8998
25°	8842
30°	8654
35°	7415
40°	4343
45°	3238
50°	2943
55°	2846
60°	2717
65°	2636
70°	2542
75°	2477
80°	2376
85°	2283

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3238 cd/sqm

TEST NUMBER: P865867

CATALOG NUMBER: PRLX-2004-S-940-10L-L-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.9	5.7
10°-20°	153.4	15.7
20°-30°	226.2	23.1
30°-40°	219.4	22.4
40°-50°	113.1	11.5
50°-60°	89.4	9.1
60°-70°	67.6	6.9
70°-80°	41.2	4.2
80°-90°	13.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.5	44.5
0°-40°	655.0	66.9
0°-60°	857.5	87.5
0°-90°	979.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	979.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	611	
5°	593	56
15°	545	153
25°	491	226
35°	372	219
45°	140	113
55°	100	89
65°	68	68
75°	39	41
85°	12	13
90°	0	

TEST NUMBER: P865867

CATALOG NUMBER: PRLX-2004-S-940-10L-L-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	611.0
2.5°	607.3
5°	593.3
7.5°	580.2
10°	568.0
12.5°	555.8
15°	544.6
17.5°	531.5
20°	518.4
22.5°	505.3
25°	491.3
27.5°	476.3
30°	459.5
32.5°	428.6
35°	372.4
37.5°	285.4
40°	204.0
42.5°	163.8
45°	140.4
47.5°	124.5
50°	116.0
52.5°	108.5
55°	100.1
57.5°	91.7
60°	83.3
62.5°	75.8
65°	68.3
67.5°	60.8
70°	53.3
72.5°	45.9
75°	39.3
77.5°	31.8
80°	25.3
82.5°	18.7
85°	12.2
87.5°	5.6
90°	0.0



TEST NUMBER: P865867
 CATALOG NUMBER: PRLX-2004-S-940-10L-L-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.10	15.46	14.47	15.78	16.09	14.10	15.46	14.47	15.78	16.09
	3H	15.92	17.14	16.30	17.47	17.84	15.92	17.14	16.30	17.47	17.84
	4H	16.65	17.80	17.06	18.15	18.53	16.65	17.80	17.06	18.15	18.53
	6H	17.23	18.28	17.64	18.65	19.04	17.23	18.28	17.64	18.65	19.04
	8H	17.44	18.44	17.87	18.83	19.23	17.44	18.44	17.87	18.83	19.23
	12H	17.59	18.55	18.02	18.93	19.36	17.59	18.55	18.02	18.93	19.36
4H	2H	14.69	15.84	15.10	16.19	16.57	14.69	15.84	15.10	16.19	16.57
	3H	16.74	17.69	17.15	18.09	18.50	16.74	17.69	17.15	18.09	18.50
	4H	17.61	18.46	18.04	18.88	19.32	17.61	18.46	18.04	18.88	19.32
	6H	18.32	19.07	18.78	19.51	19.97	18.32	19.07	18.78	19.51	19.97
	8H	18.59	19.28	19.05	19.73	20.20	18.59	19.28	19.05	19.73	20.20
	12H	18.79	19.41	19.28	19.89	20.36	18.79	19.41	19.28	19.89	20.36
8H	4H	17.92	18.62	18.39	19.06	19.53	17.92	18.62	18.39	19.06	19.53
	6H	18.78	19.35	19.28	19.85	20.33	18.78	19.35	19.28	19.85	20.33
	8H	19.14	19.65	19.66	20.17	20.66	19.14	19.65	19.66	20.17	20.66
	12H	19.45	19.89	19.96	20.39	20.96	19.45	19.89	19.96	20.39	20.96
12H	4H	17.95	18.57	18.44	19.05	19.52	17.95	18.57	18.44	19.05	19.52
	6H	18.85	19.36	19.37	19.88	20.37	18.85	19.36	19.37	19.88	20.37
	8H	19.28	19.72	19.79	20.22	20.79	19.28	19.72	19.79	20.22	20.79