

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865870

Luminaire Tested: PRLX-2004-S-940-15L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865870
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-940-15L-G-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 291.1 lumens
Efficiency: N/A
Efficacy: 18.7 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.16
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 15.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865870

CATALOG NUMBER: PRLX-2004-S-940-15L-G-U-S-X-X-GREY-X

Luminous Intensity Polar Plot



TEST NUMBER: P865870

CATALOG NUMBER: PRLX-2004-S-940-15L-G-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90				
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80				
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72				
4	91	81	74	69	89	80	74	68	78	72	68	76	71	67	74	69	66	64				
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58				
6	79	68	61	55	78	67	60	55	66	59	55	64	59	54	63	58	54	52				
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47				
8	70	58	51	46	68	57	51	46	56	50	45	55	49	45	54	49	45	43				
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40				
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2830
5°	2834
10°	2832
15°	2808
20°	2770
25°	2705
30°	2578
35°	2286
40°	1918
45°	1515
50°	1089
55°	671
60°	395
65°	336
70°	300
75°	265
80°	254
85°	243

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1515 cd/sqm

TEST NUMBER: P865870

CATALOG NUMBER: PRLX-2004-S-940-15L-G-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.5	5.7
10°-20°	46.9	16.1
20°-30°	68.9	23.7
30°-40°	71.3	24.5
40°-50°	50.7	17.4
50°-60°	22.2	7.6
60°-70°	8.7	3.0
70°-80°	4.6	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	132.3	45.4
0°-40°	203.5	69.9
0°-60°	276.4	94.9
0°-90°	291.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	291.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	174	
5°	173	16
15°	166	47
25°	150	69
35°	115	71
45°	66	51
55°	24	22
65°	9	9
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P865870

CATALOG NUMBER: PRLX-2004-S-940-15L-G-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	173.5
2.5°	173.5
5°	173.1
7.5°	172.2
10°	171.0
12.5°	169.0
15°	166.3
17.5°	163.2
20°	159.6
22.5°	155.2
25°	150.3
27.5°	144.6
30°	136.9
32.5°	126.5
35°	114.8
37.5°	102.6
40°	90.1
42.5°	77.8
45°	65.7
47.5°	54.2
50°	42.9
52.5°	32.7
55°	23.6
57.5°	16.3
60°	12.1
62.5°	10.1
65°	8.7
67.5°	7.4
70°	6.3
72.5°	5.2
75°	4.2
77.5°	3.5
80°	2.7
82.5°	2.0
85°	1.3
87.5°	0.6
90°	0.0

TEST NUMBER: P865870
 CATALOG NUMBER: PRLX-2004-S-940-15L-G-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.31	7.61	6.68	7.92	8.23	6.31	7.61	6.68	7.92	8.23
	3H	7.23	8.38	7.61	8.71	9.07	7.23	8.38	7.61	8.71	9.07
	4H	7.59	8.65	7.99	9.00	9.38	7.59	8.65	7.99	9.00	9.38
	6H	7.88	8.86	8.30	9.23	9.62	7.88	8.86	8.30	9.23	9.62
	8H	7.99	8.91	8.42	9.30	9.71	7.99	8.91	8.42	9.30	9.71
	12H	8.06	8.94	8.49	9.32	9.75	8.06	8.94	8.49	9.32	9.75
4H	2H	6.55	7.61	6.95	7.96	8.35	6.55	7.61	6.95	7.96	8.35
	3H	7.69	8.56	8.11	8.96	9.37	7.69	8.56	8.11	8.96	9.37
	4H	8.16	8.93	8.60	9.35	9.80	8.16	8.93	8.60	9.35	9.80
	6H	8.59	9.25	9.05	9.70	10.17	8.59	9.25	9.05	9.70	10.17
	8H	8.74	9.36	9.21	9.81	10.28	8.74	9.36	9.21	9.81	10.28
	12H	8.85	9.40	9.34	9.89	10.36	8.85	9.40	9.34	9.89	10.36
8H	4H	8.30	8.93	8.77	9.37	9.84	8.30	8.93	8.77	9.37	9.84
	6H	8.84	9.35	9.34	9.85	10.33	8.84	9.35	9.34	9.85	10.33
	8H	9.07	9.52	9.59	10.04	10.53	9.07	9.52	9.59	10.04	10.53
	12H	9.26	9.67	9.78	10.16	10.74	9.26	9.67	9.78	10.16	10.74
12H	4H	8.30	8.85	8.79	9.33	9.81	8.30	8.85	8.79	9.33	9.81
	6H	8.86	9.32	9.38	9.84	10.33	8.86	9.32	9.38	9.84	10.33
	8H	9.14	9.55	9.66	10.04	10.61	9.14	9.55	9.66	10.04	10.61