

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702185

Luminaire Tested: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GCC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-8)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GCC
Description: FARALLON 4" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA
Light Source: 2700K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2562.7 lumens
Efficiency: N/A
Efficacy: 63.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.34' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702185

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GCC

Luminous Intensity Polar Plot



TEST NUMBER: P702185

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GCC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99 | | 99 | 98 | 96 | | 96 | 94 | 93 | 91 |
| 2 | 106 | 101 | 96 | 92 | 104 | 99 | 95 | 91 | 95 | 92 | 89 | | 92 | 89 | 87 | | 89 | 87 | 85 | 83 |
| 3 | 100 | 93 | 87 | 83 | 98 | 91 | 86 | 82 | 88 | 84 | 80 | | 86 | 82 | 79 | | 84 | 81 | 78 | 76 |
| 4 | 94 | 86 | 79 | 75 | 92 | 85 | 79 | 74 | 82 | 77 | 73 | | 80 | 76 | 72 | | 78 | 75 | 72 | 70 |
| 5 | 89 | 80 | 73 | 68 | 87 | 79 | 72 | 68 | 77 | 71 | 67 | | 75 | 70 | 67 | | 73 | 69 | 66 | 64 |
| 6 | 84 | 74 | 68 | 63 | 82 | 73 | 67 | 63 | 72 | 66 | 62 | | 70 | 65 | 62 | | 69 | 65 | 61 | 60 |
| 7 | 79 | 69 | 63 | 58 | 78 | 69 | 62 | 58 | 67 | 62 | 58 | | 66 | 61 | 57 | | 65 | 60 | 57 | 55 |
| 8 | 75 | 65 | 58 | 54 | 74 | 64 | 58 | 54 | 63 | 58 | 54 | | 62 | 57 | 53 | | 61 | 56 | 53 | 52 |
| 9 | 71 | 61 | 55 | 50 | 70 | 61 | 54 | 50 | 60 | 54 | 50 | | 59 | 53 | 50 | | 58 | 53 | 50 | 48 |
| 10 | 68 | 58 | 51 | 47 | 67 | 57 | 51 | 47 | 56 | 51 | 47 | | 55 | 50 | 47 | | 55 | 50 | 47 | 45 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 315045 |
| 5° | 303954 |
| 10° | 289249 |
| 15° | 278201 |
| 20° | 236029 |
| 25° | 196900 |
| 30° | 147372 |
| 35° | 105824 |
| 40° | 83500 |
| 45° | 55375 |
| 50° | 40454 |
| 55° | 28653 |
| 60° | 19717 |
| 65° | 16988 |
| 70° | 14853 |
| 75° | 12682 |
| 80° | 10353 |
| 85° | 10247 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 55375 cd/sqm

TEST NUMBER: P702185

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GCC

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 243.3 | 9.5 |
| 10°-20° | 631.6 | 24.6 |
| 20°-30° | 694.8 | 27.1 |
| 30°-40° | 481.8 | 18.8 |
| 40°-50° | 274.6 | 10.7 |
| 50°-60° | 130.5 | 5.1 |
| 60°-70° | 61.8 | 2.4 |
| 70°-80° | 30.2 | 1.2 |
| 80°-90° | 8.8 | 0.3 |
| 90°-100° | 3.2 | 0.1 |
| 100°-110° | 2.1 | 0.1 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1569.7 | 61.3 |
| 0°-40° | 2051.4 | 80.1 |
| 0°-60° | 2456.6 | 95.9 |
| 0°-90° | 2557.4 | 99.8 |
| 90°-120° | 5.3 | 0.2 |
| 90°-150° | 5.3 | 0.2 |
| 90°-180° | 5.0 | 0.2 |
| 0°-180° | 2562.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|------|------|------|
| 0° | 2716 | |
| 5° | 2611 | 243 |
| 15° | 2317 | 632 |
| 25° | 1539 | 695 |
| 35° | 747 | 482 |
| 45° | 338 | 275 |
| 55° | 142 | 131 |
| 65° | 62 | 62 |
| 75° | 28 | 30 |
| 85° | 8 | 8 |
| 90° | 3 | 2 |
| 95° | 3 | 2 |
| 105° | 3 | 2 |
| 115° | 0 | 0 |
| 125° | 0 | 0 |
| 135° | 0 | 0 |
| 145° | 0 | 0 |
| 155° | 0 | 0 |
| 165° | 0 | 0 |
| 175° | 0 | 0 |
| 180° | 0 | 0 |

TEST NUMBER: P702185

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GCC

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 2716.3 |
| 1° | 2700.9 |
| 2° | 2675.1 |
| 3° | 2659.6 |
| 4° | 2636.4 |
| 5° | 2610.7 |
| 6° | 2569.4 |
| 7° | 2528.2 |
| 8° | 2497.3 |
| 9° | 2484.4 |
| 10° | 2456.0 |
| 11° | 2412.2 |
| 12° | 2391.6 |
| 13° | 2381.3 |
| 14° | 2360.7 |
| 15° | 2316.9 |
| 16° | 2257.6 |
| 17° | 2177.7 |
| 18° | 2087.5 |
| 19° | 1992.1 |
| 20° | 1912.3 |
| 21° | 1842.7 |
| 22° | 1773.1 |
| 23° | 1700.9 |
| 24° | 1626.2 |
| 25° | 1538.6 |
| 27.5° | 1316.9 |
| 30° | 1100.4 |
| 32.5° | 896.9 |
| 35° | 747.4 |
| 37.5° | 639.1 |
| 40° | 551.5 |
| 42.5° | 440.7 |
| 45° | 337.6 |
| 47.5° | 270.6 |
| 50° | 224.2 |
| 52.5° | 183.0 |
| 55° | 141.7 |
| 57.5° | 108.2 |
| 60° | 85.0 |
| 62.5° | 72.2 |
| 65° | 61.9 |
| 67.5° | 51.5 |
| 70° | 43.8 |
| 72.5° | 36.1 |

TEST NUMBER: P702185

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-GCC

CANDELA DISTRIBUTION (continued):

| | 0° |
|--------|------|
| 75° | 28.3 |
| 77.5° | 20.6 |
| 80° | 15.5 |
| 82.5° | 10.3 |
| 85° | 7.7 |
| 87.5° | 5.2 |
| 90° | 2.6 |
| 92.5° | 2.6 |
| 95° | 2.6 |
| 97.5° | 2.6 |
| 100° | 5.2 |
| 102.5° | 2.6 |
| 105° | 2.6 |
| 107.5° | 0.0 |
| 110° | 0.0 |
| 112.5° | 0.0 |
| 115° | 0.0 |
| 117.5° | 0.0 |
| 120° | 0.0 |
| 122.5° | 0.0 |
| 125° | 0.0 |
| 127.5° | 0.0 |
| 130° | 0.0 |
| 132.5° | 0.0 |
| 135° | 0.0 |
| 137.5° | 0.0 |
| 140° | 0.0 |
| 142.5° | 0.0 |
| 145° | 0.0 |
| 147.5° | 0.0 |
| 150° | 0.0 |
| 152.5° | 0.0 |
| 155° | 0.0 |
| 157.5° | 0.0 |
| 160° | 0.0 |
| 162.5° | 0.0 |
| 165° | 0.0 |
| 167.5° | 0.0 |
| 170° | 0.0 |
| 172.5° | 0.0 |
| 175° | 0.0 |
| 177.5° | 0.0 |
| 180° | 0.0 |

(END OF REPORT)