

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865882

Luminaire Tested: PRLX-2004-S-940-20L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865882
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-25)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-940-20L-L-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 4
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1074.7 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.02
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865882

CATALOG NUMBER: PRLX-2004-S-940-20L-L-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P865882

CATALOG NUMBER: PRLX-2004-S-940-20L-L-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99		100	98	96		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84	81	79	77
4	95	86	80	75	93	85	79	75	83	78	74		81	76	73		79	75	72	71
5	89	80	74	69	87	79	73	68	77	72	68		75	71	67		74	70	67	65
6	84	74	68	63	83	74	67	63	72	67	63		71	66	62		69	65	62	60
7	80	70	63	58	78	69	63	58	67	62	58		66	61	58		65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	55	50	70	60	54	50	59	54	50		59	53	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	47		54	50	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	15537
5°	15199
10°	14568
15°	14000
20°	13512
25°	13067
30°	12549
35°	9762
40°	4024
45°	1596
50°	1045
55°	1012
60°	917
65°	868
70°	801
75°	826
80°	704
85°	692

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1596 cd/sqm

TEST NUMBER: P865882

CATALOG NUMBER: PRLX-2004-S-940-20L-L-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	8.1
10°-20°	233.7	21.7
20°-30°	334.2	31.1
30°-40°	284.1	26.4
40°-50°	64.6	6.0
50°-60°	31.2	2.9
60°-70°	22.7	2.1
70°-80°	13.1	1.2
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	654.9	60.9
0°-40°	939.0	87.4
0°-60°	1034.8	96.3
0°-90°	1074.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1074.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	953	
5°	928	87
15°	829	234
25°	726	334
35°	490	284
45°	69	65
55°	36	31
65°	22	23
75°	13	13
85°	4	4
90°	0	

TEST NUMBER: P865882

CATALOG NUMBER: PRLX-2004-S-940-20L-L-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	952.6
2.5°	948.9
5°	928.3
7.5°	903.9
10°	879.6
12.5°	855.3
15°	829.1
17.5°	804.7
20°	778.5
22.5°	752.3
25°	726.1
27.5°	699.9
30°	666.3
32.5°	600.8
35°	490.3
37.5°	329.4
40°	189.0
42.5°	110.4
45°	69.2
47.5°	46.8
50°	41.2
52.5°	37.4
55°	35.6
57.5°	31.8
60°	28.1
62.5°	26.2
65°	22.5
67.5°	20.6
70°	16.8
72.5°	15.0
75°	13.1
77.5°	9.4
80°	7.5
82.5°	5.6
85°	3.7
87.5°	1.9
90°	0.0

TEST NUMBER: P865882

CATALOG NUMBER: PRLX-2004-S-940-20L-L-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.78	7.85	7.15	8.16	8.47	6.78	7.85	7.15	8.16	8.47
	3H	8.42	9.36	8.80	9.70	10.07	8.42	9.36	8.80	9.70	10.07
	4H	9.10	9.98	9.51	10.33	10.72	9.10	9.98	9.51	10.33	10.72
	6H	9.51	10.31	9.93	10.69	11.08	9.51	10.31	9.93	10.69	11.08
	8H	9.67	10.42	10.10	10.81	11.22	9.67	10.42	10.10	10.81	11.22
	12H	9.77	10.49	10.21	10.88	11.31	9.77	10.49	10.21	10.88	11.31
4H	2H	7.26	8.13	7.67	8.49	8.87	7.26	8.13	7.67	8.49	8.87
	3H	9.10	9.82	9.52	10.23	10.63	9.10	9.82	9.52	10.23	10.63
	4H	9.92	10.56	10.36	10.99	11.44	9.92	10.56	10.36	10.99	11.44
	6H	10.46	11.01	10.93	11.45	11.93	10.46	11.01	10.93	11.45	11.93
	8H	10.65	11.17	11.13	11.62	12.09	10.65	11.17	11.13	11.62	12.09
	12H	10.81	11.25	11.30	11.74	12.22	10.81	11.25	11.30	11.74	12.22
8H	4H	10.15	10.66	10.62	11.11	11.58	10.15	10.66	10.62	11.11	11.58
	6H	10.81	11.22	11.32	11.72	12.21	10.81	11.22	11.32	11.72	12.21
	8H	11.10	11.46	11.63	11.98	12.48	11.10	11.46	11.63	11.98	12.48
	12H	11.35	11.67	11.87	12.16	12.74	11.35	11.67	11.87	12.16	12.74
12H	4H	10.15	10.59	10.64	11.08	11.56	10.15	10.59	10.64	11.08	11.56
	6H	10.85	11.21	11.38	11.73	12.23	10.85	11.21	11.38	11.73	12.23
	8H	11.20	11.51	11.72	12.01	12.59	11.20	11.51	11.72	12.01	12.59