

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701789

Luminaire Tested: 340-4C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P701789  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-4C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC  
Description: FARALLON 4" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.  
Light Source: 2700K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 441.7 lumens  
Efficiency: N/A  
Efficacy: 61.3 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.64  
Luminous Opening: (L: -0.34 ' x W: 0 ' x H: 0 '  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P701789

CATALOG NUMBER: 340-4C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC

### Luminous Intensity Polar Plot




TEST NUMBER: P701789

CATALOG NUMBER: 340-4C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81	78	75	73
5	91	82	76	72	89	82	76	72	80	75	71		78	74	70		76	73	70	68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72	68	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	57	56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62	57	54	53
10	71	62	56	52	70	61	55	52	60	55	52		59	55	51		59	54	51	50

**AVERAGE LUMINANCE (cd/sqm):**



**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: -  
 Vertical Angle: -  
 Luminance: -

TEST NUMBER: P701789

CATALOG NUMBER: 340-4C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.8	13.5
10°-20°	114.8	26.0
20°-30°	124.1	28.1
30°-40°	76.6	17.3
40°-50°	38.4	8.7
50°-60°	16.1	3.6
60°-70°	7.6	1.7
70°-80°	3.3	0.8
80°-90°	0.7	0.2
90°-100°	0.1	0.0
100°-110°	0.2	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	298.7	67.6
0°-40°	375.3	85.0
0°-60°	429.8	97.3
0°-90°	441.4	99.9
90°-120°	0.3	0.1
90°-150°	0.3	0.1
90°-180°	0.0	0.0
0°-180°	441.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	883	
5°	703	60
15°	413	115
25°	281	124
35°	119	77
45°	46	38
55°	18	16
65°	8	8
75°	3	3
85°	0	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P701789

CATALOG NUMBER: 340-4C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	883.4
1°	879.0
2°	854.2
3°	813.3
4°	760.3
5°	702.9
6°	645.5
7°	593.5
8°	552.1
9°	521.0
10°	496.7
11°	475.7
12°	457.7
13°	442.2
14°	428.1
15°	413.0
16°	397.9
17°	380.9
18°	365.3
19°	352.7
20°	344.4
21°	337.6
22°	328.8
23°	316.7
24°	300.1
25°	281.2
27.5°	226.2
30°	176.6
32.5°	142.5
35°	119.2
37.5°	102.2
40°	85.1
42.5°	63.7
45°	46.2
47.5°	35.0
50°	27.7
52.5°	22.9
55°	18.0
57.5°	12.6
60°	10.2
62.5°	8.8
65°	7.8
67.5°	6.3
70°	5.4
72.5°	3.9

TEST NUMBER: P701789

CATALOG NUMBER: 340-4C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC

**CANDELA DISTRIBUTION (continued):**

	0°
75°	2.9
77.5°	2.4
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.5
102.5°	0.5
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)