

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701810

Luminaire Tested: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-CC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P701810
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-3)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-CC
Description: FARALLON 4" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 593.4 lumens
Efficiency: N/A
Efficacy: 59.9 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.64
Luminous Opening: Circular (Dia: 0.34' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P701810

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-CC

Luminous Intensity Polar Plot



TEST NUMBER: P701810

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-CC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81	78	75	73
5	91	82	76	72	89	82	76	72	80	75	71		78	74	70		76	73	70	68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72	68	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	57	56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62	57	54	53
10	71	62	56	52	70	61	55	52	60	55	52		59	55	51		59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	137649
5°	109941
10°	78590
15°	66617
20°	57110
25°	48336
30°	31767
35°	22668
40°	17321
45°	10186
50°	6730
55°	4893
60°	3178
65°	2882
70°	2442
75°	1748
80°	1336
85°	932

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10186 cd/sqm

TEST NUMBER: P701810

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-CC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.3	13.5
10°-20°	154.3	26.0
20°-30°	166.6	28.1
30°-40°	102.9	17.3
40°-50°	51.6	8.7
50°-60°	21.6	3.6
60°-70°	10.2	1.7
70°-80°	4.5	0.8
80°-90°	1.0	0.2
90°-100°	0.1	0.0
100°-110°	0.3	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	401.2	67.6
0°-40°	504.2	85.0
0°-60°	577.4	97.3
0°-90°	593.1	99.9
90°-120°	0.4	0.1
90°-150°	0.4	0.1
90°-180°	0.0	0.0
0°-180°	593.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1187	
5°	944	80
15°	555	154
25°	378	167
35°	160	103
45°	62	52
55°	24	22
65°	10	10
75°	4	4
85°	1	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P701810

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-CC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1186.8
1°	1180.9
2°	1147.6
3°	1092.7
4°	1021.5
5°	944.3
6°	867.2
7°	797.3
8°	741.8
9°	699.9
10°	667.3
11°	639.1
12°	615.0
13°	594.1
14°	575.1
15°	554.8
16°	534.6
17°	511.7
18°	490.8
19°	473.8
20°	462.7
21°	453.5
22°	441.8
23°	425.4
24°	403.2
25°	377.7
27.5°	303.9
30°	237.2
32.5°	191.5
35°	160.1
37.5°	137.2
40°	114.4
42.5°	85.6
45°	62.1
47.5°	47.1
50°	37.3
52.5°	30.7
55°	24.2
57.5°	17.0
60°	13.7
62.5°	11.8
65°	10.5
67.5°	8.5
70°	7.2
72.5°	5.2

TEST NUMBER: P701810

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-CC

CANDELA DISTRIBUTION (continued):

	0°
75°	3.9
77.5°	3.3
80°	2.0
82.5°	1.3
85°	0.7
87.5°	0.7
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.7
102.5°	0.7
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)