

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701852

Luminaire Tested: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P701852  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CC  
Description: FARALLON 4" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.  
Light Source: 3000K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 616.8 lumens  
Efficiency: N/A  
Efficacy: 62.3 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.64  
Luminous Opening: Circular (Dia: 0.34' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P701852

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CC

### Luminous Intensity Polar Plot



TEST NUMBER: P701852

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81	78	75	73
5	91	82	76	72	89	82	76	72	80	75	71		78	74	70		76	73	70	68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72	68	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	57	56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62	57	54	53
10	71	62	56	52	70	61	55	52	60	55	52		59	55	51		59	54	51	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	143088
5°	114296
10°	81687
15°	69259
20°	59368
25°	50255
30°	33026
35°	23560
40°	18002
45°	10580
50°	6983
55°	5075
60°	3317
65°	2991
70°	2543
75°	1837
80°	1336
85°	932

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10580 cd/sqm

TEST NUMBER: P701852

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.5	13.5
10°-20°	160.4	26.0
20°-30°	173.2	28.1
30°-40°	107.0	17.4
40°-50°	53.6	8.7
50°-60°	22.5	3.6
60°-70°	10.6	1.7
70°-80°	4.6	0.8
80°-90°	1.0	0.2
90°-100°	0.1	0.0
100°-110°	0.3	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	417.1	67.6
0°-40°	524.1	85.0
0°-60°	600.2	97.3
0°-90°	616.5	99.9
90°-120°	0.4	0.1
90°-150°	0.4	0.1
90°-180°	0.0	0.0
0°-180°	616.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1234	
5°	982	83
15°	577	160
25°	393	173
35°	166	107
45°	64	54
55°	25	22
65°	11	11
75°	4	5
85°	1	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P701852

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1233.7
1°	1227.6
2°	1193.0
3°	1135.9
4°	1061.8
5°	981.7
6°	901.5
7°	828.8
8°	771.1
9°	727.6
10°	693.6
11°	664.4
12°	639.3
13°	617.5
14°	597.8
15°	576.8
16°	555.7
17°	531.9
18°	510.2
19°	492.5
20°	481.0
21°	471.5
22°	459.2
23°	442.3
24°	419.2
25°	392.7
27.5°	315.9
30°	246.6
32.5°	199.1
35°	166.4
37.5°	142.7
40°	118.9
42.5°	89.0
45°	64.5
47.5°	48.9
50°	38.7
52.5°	31.9
55°	25.1
57.5°	17.7
60°	14.3
62.5°	12.2
65°	10.9
67.5°	8.8
70°	7.5
72.5°	5.4

TEST NUMBER: P701852

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CC

**CANDELA DISTRIBUTION (continued):**

	0°
75°	4.1
77.5°	3.4
80°	2.0
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.7
102.5°	0.7
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)