

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: G2-2210-802-47

Luminaire Tested: PRLX-403-FR-120-BKMT-RHL-TFIN-DB-BK

Test Date: 1/5/2023



Test Information

Test Method: LM-79-2019
Report Number: G2-2210-802-47
Test Lab: COOPER LIGHTING SOLUTIONS
Test Date: 1/5/2023
Issue Date: 1/5/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-403-FR-120-BKMT-RHL-TFIN-DB-BK
Description: 400-SERIES 3D PRINTED LED LAMP BASED DECORATIVE LUMINAIRE, BLACK (OPAQUE) SHADE, FROSTED LAMP
Light Source: 1 PHILIPS 60W FROSTED BULB
FROSTED BULB - 60W EQUIVALENT 929002036204 8.8A19/PER/930/P/E26/DIM
6/1FB T20. PHILIPS
Ballast/Driver: INTEGRAL TO LAMP

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 225.2 lumens
Efficiency: N/A
Efficacy: 29.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.32
Luminous Opening: Vertical Cylinder (Dia: 0.67' x H: 0.92')
CIE Type: Direct

Input Watts (W): 7.7
Input Voltage (V): 120.0
Input Current (A_{in}): 0.0679
Voltage Rise (V): NR
Power Factor: 0.9502
Total Harmonic Distortion (THDi): 24.3%
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): 25.4
Test Distance: 24 FT

TEST NUMBER: G2-2210-802-47

CATALOG NUMBER: PRLX-403-FR-120-BKMT-RHL-TFIN-DB-BK

Luminous Intensity Polar Plot





TEST NUMBER: G2-2210-802-47

CATALOG NUMBER: PRLX-403-FR-120-BKMT-RHL-TFIN-DB-BK

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91				91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81				81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73				73
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65				65
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58				58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	54	63	58	54	52				52
7	74	63	55	50	72	62	55	50	60	54	50	59	53	49	58	53	49	47				47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	44	43				43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39				39
10	61	49	42	38	60	49	42	38	48	42	37	47	41	37	46	41	37	36				36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3636
5°	3135
10°	2737
15°	2453
20°	2217
25°	2029
30°	1891
35°	1764
40°	1454
45°	1035
50°	616
55°	263
60°	41
65°	18
70°	14
75°	9
80°	6
85°	3

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1035 cd/sqm



TEST NUMBER: G2-2210-802-47

CATALOG NUMBER: PRLX-403-FR-120-BKMT-RHL-TFIN-DB-BK

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.1	4.9
10°-20°	31.9	14.2
20°-30°	50.2	22.3
30°-40°	63.7	28.3
40°-50°	49.8	22.1
50°-60°	16.4	7.3
60°-70°	1.3	0.6
70°-80°	0.6	0.3
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	93.1	41.4
0°-40°	156.8	69.6
0°-60°	223.0	99.0
0°-90°	225.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	225.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	118	
5°	117	11
15°	113	32
25°	108	50
35°	104	64
45°	65	50
55°	17	16
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: G2-2210-802-47

CATALOG NUMBER: PRLX-403-FR-120-BKMT-RHL-TFIN-DB-BK

CANDELA DISTRIBUTION (FULL):

	0°
0°	117.9
2.5°	117.2
5°	116.8
7.5°	115.8
10°	114.4
12.5°	113.5
15°	112.9
17.5°	111.9
20°	110.6
22.5°	109.3
25°	108.3
27.5°	107.7
30°	106.8
32.5°	105.8
35°	104.3
37.5°	98.7
40°	89.2
42.5°	77.8
45°	65.3
47.5°	52.5
50°	39.6
52.5°	27.8
55°	17.1
57.5°	8.4
60°	2.7
62.5°	1.4
65°	1.2
67.5°	1.0
70°	0.9
72.5°	0.7
75°	0.6
77.5°	0.5
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)