

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701842

Luminaire Tested: 340-4C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-GCC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P701842
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-8)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-GCC
Description: FARALLON 4" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 700.0 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.34' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P701842

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-GCC

Luminous Intensity Polar Plot



TEST NUMBER: P701842

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-GCC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	94	93	91
2	106	101	96	92	104	99	95	91	95	92	89		92	89	87		89	87	85	83
3	100	93	87	83	98	91	86	82	88	84	80		86	82	79		84	81	78	76
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78	75	72	70
5	89	80	73	68	87	79	72	68	77	71	67		75	70	67		73	69	66	64
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69	65	61	60
7	79	69	63	58	78	69	62	58	67	62	58		66	61	57		65	60	57	55
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	56	53	52
9	71	61	55	50	70	61	54	50	60	54	50		59	53	50		58	53	50	48
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86060
5°	83035
10°	79013
15°	75995
20°	64478
25°	53787
30°	40258
35°	28913
40°	22817
45°	15123
50°	11043
55°	7826
60°	5382
65°	4638
70°	4069
75°	3451
80°	2805
85°	2795

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15123 cd/sqm

TEST NUMBER: P701842

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-GCC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	9.5
10°-20°	172.5	24.6
20°-30°	189.8	27.1
30°-40°	131.6	18.8
40°-50°	75.0	10.7
50°-60°	35.7	5.1
60°-70°	16.9	2.4
70°-80°	8.2	1.2
80°-90°	2.4	0.3
90°-100°	0.9	0.1
100°-110°	0.6	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	428.8	61.3
0°-40°	560.4	80.1
0°-60°	671.1	95.9
0°-90°	698.6	99.8
90°-120°	1.4	0.2
90°-150°	1.4	0.2
90°-180°	1.0	0.1
0°-180°	700.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	742	
5°	713	66
15°	633	173
25°	420	190
35°	204	132
45°	92	75
55°	39	36
65°	17	17
75°	8	8
85°	2	2
90°	1	0
95°	1	1
105°	1	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P701842

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-GCC

CANDELA DISTRIBUTION (FULL):

0°	
0°	742.0
1°	737.8
2°	730.8
3°	726.5
4°	720.2
5°	713.2
6°	701.9
7°	690.6
8°	682.2
9°	678.7
10°	670.9
11°	659.0
12°	653.3
13°	650.5
14°	644.9
15°	632.9
16°	616.7
17°	594.9
18°	570.2
19°	544.2
20°	522.4
21°	503.4
22°	484.4
23°	464.6
24°	444.2
25°	420.3
27.5°	359.7
30°	300.6
32.5°	245.0
35°	204.2
37.5°	174.6
40°	150.7
42.5°	120.4
45°	92.2
47.5°	73.9
50°	61.2
52.5°	50.0
55°	38.7
57.5°	29.6
60°	23.2
62.5°	19.7
65°	16.9
67.5°	14.1
70°	12.0
72.5°	9.9

TEST NUMBER: P701842

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9050-4LBW1LI-GCC

CANDELA DISTRIBUTION (continued):

	0°
75°	7.7
77.5°	5.6
80°	4.2
82.5°	2.8
85°	2.1
87.5°	1.4
90°	0.7
92.5°	0.7
95°	0.7
97.5°	0.7
100°	1.4
102.5°	0.7
105°	0.7
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)