

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: G2-2210-802-51

Luminaire Tested: PRLX-411-FR-120-BKMT-RHL-TFIN-DB-BK

Test Date: 1/8/2023



Test Information

Test Method: LM-79-2019
Report Number: G2-2210-802-51
Test Lab: COOPER LIGHTING SOLUTIONS
Test Date: 1/8/2023
Issue Date: 1/8/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-411-FR-120-BKMT-RHL-TFIN-DB-BK
Description: 400-SERIES 3D PRINTED LED LAMP BASED DECORATIVE LUMINAIRE, BLACK (OPAQUE) SHADE, FROSTED LAMP
Light Source: 1 PHILIPS 60W FROSTED BULB
FROSTED BULB - 60W EQUIVALENT 929002036204 8.8A19/PER/930/P/E26/DIM
6/1FB T20. PHILIPS
Ballast/Driver: INTEGRAL TO LAMP


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 259.2 lumens
Efficiency: N/A
Efficacy: 32.8 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.46
Luminous Opening: Vertical Cylinder (Dia: 1.17' x H: 1.17')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): 120.0
Input Current (Ain): 0.0689
Voltage Rise (V): NR
Power Factor: 0.9536
Total Harmonic Distortion (THDi): 23.2%
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): 24.8
Test Distance: 24 FT

TEST NUMBER: G2-2210-802-51
CATALOG NUMBER: PRLX-411-FR-120-BKMT-RHL-TFIN-DB-BK

Luminous Intensity Polar Plot





TEST NUMBER: G2-2210-802-51

CATALOG NUMBER: PRLX-411-FR-120-BKMT-RHL-TFIN-DB-BK

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	82	77	95	87	81	77	85	80	75		82	78	74		80	76	73	71
4	90	80	73	68	88	79	73	67	77	71	67		75	70	66		73	68	65	63
5	84	73	65	60	82	72	65	60	70	64	59		68	63	58		66	62	58	56
6	78	66	59	53	76	65	58	53	64	57	53		62	57	52		61	56	52	50
7	72	61	53	48	71	60	53	47	58	52	47		57	51	47		56	51	47	45
8	68	56	48	43	66	55	48	43	54	47	42		52	47	42		51	46	42	40
9	63	51	44	39	62	51	43	39	49	43	38		48	42	38		47	42	38	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1299
5°	1150
10°	997
15°	892
20°	818
25°	764
30°	724
35°	691
40°	667
45°	633
50°	403
55°	137
60°	11
65°	8
70°	7
75°	5
80°	3
85°	1

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 633 cd/sqm



TEST NUMBER: G2-2210-802-51

CATALOG NUMBER: PRLX-411-FR-120-BKMT-RHL-TFIN-DB-BK

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.8	4.6
10°-20°	32.5	12.5
20°-30°	50.7	19.6
30°-40°	66.8	25.8
40°-50°	72.4	27.9
50°-60°	22.8	8.8
60°-70°	1.3	0.5
70°-80°	0.7	0.3
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	95.1	36.7
0°-40°	161.8	62.4
0°-60°	257.0	99.1
0°-90°	259.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	259.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	129	
5°	126	12
15°	115	32
25°	110	51
35°	106	67
45°	101	72
55°	22	23
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: G2-2210-802-51

CATALOG NUMBER: PRLX-411-FR-120-BKMT-RHL-TFIN-DB-BK

CANDELA DISTRIBUTION (FULL):

	0°
0°	129.0
2.5°	128.0
5°	126.4
7.5°	123.5
10°	119.4
12.5°	116.4
15°	114.7
17.5°	113.2
20°	111.7
22.5°	110.4
25°	109.6
27.5°	108.9
30°	108.1
32.5°	107.0
35°	106.3
37.5°	105.6
40°	104.9
42.5°	104.1
45°	101.0
47.5°	85.9
50°	64.8
52.5°	42.7
55°	22.0
57.5°	6.2
60°	1.7
62.5°	1.5
65°	1.3
67.5°	1.1
70°	1.0
72.5°	0.8
75°	0.7
77.5°	0.5
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)