

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P701285

Luminaire Tested: PRLX-UHBS-1218-MV-L84050-BLAK(4000K_L15_120V)

Issue Date: 8/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P701285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2305-038-1)
Test Lab: INNOVATION CENTER
Issue Date: 8/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-UHBS-1218-MV-L84050-BLAK(4000K_L15_120V)
Description: PRENTALUX HIGH BAY LUMINAIRE WITH BLACK SHADE
LIGHT LEVEL - 15,0000 NOMINAL LUMENS
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9138.4 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.14
Luminous Opening: Vertical Cylinder (Dia: 1.35' x H: 1.04')
CIE Type: Direct

Input Watts (W): 98.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P701285

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K_L15_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P701285

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K_L15_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		101	101	101	99
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	94	93	91
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89	87	85	83
3	100	92	86	82	97	91	85	81	88	83	80		85	82	78		83	80	77	75
4	93	85	78	74	91	84	78	73	81	76	72		79	75	71		77	73	70	69
5	88	78	71	66	86	77	71	66	75	70	65		73	68	65		72	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62	57	54	52
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58	53	49	48
9	69	58	51	46	67	57	51	46	56	50	46		55	50	46		54	49	46	44
10	65	54	47	43	64	53	47	43	52	46	42		51	46	42		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43803
5°	40500
10°	37722
15°	35493
20°	33590
25°	31843
30°	28021
35°	21010
40°	15375
45°	11251
50°	5960
55°	304
60°	194
65°	177
70°	160
75°	124
80°	79
85°	42

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11251 cd/sqm



TEST NUMBER: P701285

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K_L15_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	558.3	6.1
10°-20°	1639.0	17.9
20°-30°	2564.8	28.1
30°-40°	2437.8	26.7
40°-50°	1581.7	17.3
50°-60°	236.2	2.6
60°-70°	30.7	0.3
70°-80°	20.7	0.2
80°-90°	7.1	0.1
90°-100°	8.9	0.1
100°-110°	9.5	0.1
110°-120°	8.9	0.1
120°-130°	8.4	0.1
130°-140°	8.7	0.1
140°-150°	7.9	0.1
150°-160°	6.0	0.1
160°-170°	3.0	0.0
170°-180°	0.8	0.0
0°-30°	4762.1	52.1
0°-40°	7199.9	78.8
0°-60°	9017.8	98.7
0°-90°	9076.3	99.3
90°-120°	27.3	0.3
90°-150°	52.3	0.6
90°-180°	62.0	0.7
0°-180°	9138.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5861	
5°	5861	558
15°	5791	1639
25°	5625	2565
35°	3882	2438
45°	2107	1582
55°	56	236
65°	31	31
75°	20	21
85°	6	6
90°	4	3
95°	9	7
105°	9	10
115°	9	9
125°	9	8
135°	11	9
145°	13	8
155°	13	6
165°	10	3
175°	8	1
180°	8	

TEST NUMBER: P701285

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K_L15_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	5861
2.5°	5864
5°	5861
7.5°	5847
10°	5829
12.5°	5812
15°	5791
17.5°	5766
20°	5729
22.5°	5680
25°	5625
27.5°	5514
30°	5083
32.5°	4523
35°	3882
37.5°	3319
40°	2871
42.5°	2485
45°	2107
47.5°	1679
50°	1111
52.5°	423
55°	56
57.5°	38
60°	35
62.5°	33
65°	31
67.5°	29
70°	27
72.5°	23
75°	20
77.5°	16
80°	12
82.5°	9
85°	6
87.5°	3
90°	4
92.5°	8
95°	9
97.5°	9
100°	9
102.5°	9
105°	9
107.5°	9
110°	9

TEST NUMBER: P701285

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K_L15_120V)

CANDELA DISTRIBUTION (continued):

	0°
112.5°	9
115°	9
117.5°	9
120°	9
122.5°	9
125°	9
127.5°	10
130°	10
132.5°	11
135°	11
137.5°	12
140°	12
142.5°	12
145°	13
147.5°	13
150°	13
152.5°	13
155°	13
157.5°	13
160°	12
162.5°	12
165°	10
167.5°	9
170°	9
172.5°	8
175°	8
177.5°	8
180°	8

(END OF REPORT)