

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P701283

Luminaire Tested: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L18\_120V)

Issue Date: 8/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P701283  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2305-038-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L18\_120V)  
Description: PRENTALUX HIGH BAY LUMINAIRE WITH BLACK SHADE  
LIGHT LEVEL - 18,000 NOMINAL LUMENS  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10597.7 lumens  
Efficiency: N/A  
Efficacy: 90.0 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.14  
Luminous Opening: Vertical Cylinder (Dia: 1.35' x H: 1.04')  
CIE Type: Direct

Input Watts (W): 117.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P701283

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L18\_120V)

### Luminous Intensity Polar Plot





TEST NUMBER: P701283

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L18\_120V)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		101	101	101	99
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	94	93	91
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89	87	85	83
3	100	92	86	82	97	91	85	81	88	83	80		85	82	78		83	80	77	75
4	93	85	78	74	91	84	78	73	81	76	72		79	75	71		77	73	70	69
5	88	78	71	66	86	77	71	66	75	70	65		73	68	65		72	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62	57	54	52
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58	53	49	48
9	69	58	51	46	67	57	51	46	56	50	46		55	50	46		54	49	46	44
10	65	54	47	43	64	53	47	43	52	46	42		51	46	42		51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	50799
5°	46968
10°	43746
15°	41161
20°	38955
25°	36928
30°	32496
35°	24365
40°	17830
45°	13047
50°	6912
55°	353
60°	225
65°	205
70°	185
75°	144
80°	91
85°	49

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13047 cd/sqm



TEST NUMBER: P701283

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L18\_120V)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	647.5	6.1
10°-20°	1900.8	17.9
20°-30°	2974.4	28.1
30°-40°	2827.1	26.7
40°-50°	1834.3	17.3
50°-60°	273.9	2.6
60°-70°	35.6	0.3
70°-80°	24.0	0.2
80°-90°	8.2	0.1
90°-100°	10.3	0.1
100°-110°	11.0	0.1
110°-120°	10.3	0.1
120°-130°	9.7	0.1
130°-140°	10.1	0.1
140°-150°	9.2	0.1
150°-160°	6.9	0.1
160°-170°	3.5	0.0
170°-180°	0.9	0.0
0°-30°	5522.6	52.1
0°-40°	8349.8	78.8
0°-60°	10458.0	98.7
0°-90°	10525.8	99.3
90°-120°	31.6	0.3
90°-150°	60.6	0.6
90°-180°	72.0	0.7
0°-180°	10597.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6797	
5°	6797	648
15°	6716	1901
25°	6523	2974
35°	4502	2827
45°	2444	1834
55°	65	274
65°	36	36
75°	23	24
85°	7	7
90°	5	3
95°	10	8
105°	10	11
115°	10	10
125°	10	10
135°	13	10
145°	15	9
155°	15	7
165°	12	3
175°	9	1
180°	9	

TEST NUMBER: P701283

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L18\_120V)

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6797.0
2.5°	6800.5
5°	6797.0
7.5°	6780.8
10°	6759.9
12.5°	6740.2
15°	6715.8
17.5°	6686.9
20°	6643.9
22.5°	6587.1
25°	6523.3
27.5°	6394.6
30°	5894.8
32.5°	5245.3
35°	4502.0
37.5°	3849.1
40°	3329.5
42.5°	2881.9
45°	2443.5
47.5°	1947.1
50°	1288.4
52.5°	490.6
55°	64.9
57.5°	44.1
60°	40.6
62.5°	38.3
65°	36.0
67.5°	33.6
70°	31.3
72.5°	26.7
75°	23.2
77.5°	18.6
80°	13.9
82.5°	10.4
85°	7.0
87.5°	3.5
90°	4.6
92.5°	9.3
95°	10.4
97.5°	10.4
100°	10.4
102.5°	10.4
105°	10.4
107.5°	10.4
110°	10.4

TEST NUMBER: P701283

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L18\_120V)

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	10.4
115°	10.4
117.5°	10.4
120°	10.4
122.5°	10.4
125°	10.4
127.5°	11.6
130°	11.6
132.5°	12.8
135°	12.8
137.5°	13.9
140°	13.9
142.5°	13.9
145°	15.1
147.5°	15.1
150°	15.1
152.5°	15.1
155°	15.1
157.5°	15.1
160°	13.9
162.5°	13.9
165°	11.6
167.5°	10.4
170°	10.4
172.5°	9.3
175°	9.3
177.5°	9.3
180°	9.3

(END OF REPORT)