

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P709441

Luminaire Tested: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L12\_277V)

Issue Date: 8/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P709441  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2305-038-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L12\_277V)  
Description: PRENATALUX HIGH BAY LUMINAIRE WITH BLACK SHADE  
LIGHT LEVEL - 12,0000 NOMINAL LUMENS  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7625.9 lumens  
Efficiency: N/A  
Efficacy: 95.8 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.14  
Luminous Opening: Vertical Cylinder (Dia: 1.35' x H: 1.04')  
CIE Type: Direct

Input Watts (W): 79.6  
Input Voltage (V): 277  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P709441

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L12\_277V)

### Luminous Intensity Polar Plot





TEST NUMBER: P709441

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L12\_277V)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		101	101	101	99
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	94	93	91
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89	87	85	83
3	100	92	86	82	97	91	85	81	88	83	80		85	82	78		83	80	77	75
4	93	85	78	74	91	84	78	73	81	76	72		79	75	71		77	73	70	69
5	88	78	71	66	86	77	71	66	75	70	65		73	68	65		72	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62	57	54	52
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58	53	49	48
9	69	58	51	46	67	57	51	46	56	50	46		55	50	46		54	49	46	44
10	65	54	47	43	64	53	47	43	52	46	42		51	46	42		51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	36553
5°	33797
10°	31478
15°	29618
20°	28031
25°	26572
30°	23383
35°	17532
40°	12830
45°	9388
50°	4974
55°	254
60°	162
65°	148
70°	133
75°	104
80°	66
85°	35

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9388 cd/sqm



TEST NUMBER: P709441

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L12\_277V)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	465.9	6.1
10°-20°	1367.8	17.9
20°-30°	2140.3	28.1
30°-40°	2034.3	26.7
40°-50°	1319.9	17.3
50°-60°	197.1	2.6
60°-70°	25.6	0.3
70°-80°	17.3	0.2
80°-90°	5.9	0.1
90°-100°	7.4	0.1
100°-110°	7.9	0.1
110°-120°	7.4	0.1
120°-130°	7.0	0.1
130°-140°	7.3	0.1
140°-150°	6.6	0.1
150°-160°	5.0	0.1
160°-170°	2.5	0.0
170°-180°	0.7	0.0
0°-30°	3974.0	52.1
0°-40°	6008.2	78.8
0°-60°	7525.2	98.7
0°-90°	7574.0	99.3
90°-120°	22.8	0.3
90°-150°	43.7	0.6
90°-180°	52.0	0.7
0°-180°	7625.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4891	
5°	4891	466
15°	4832	1368
25°	4694	2140
35°	3239	2034
45°	1758	1320
55°	47	197
65°	26	26
75°	17	17
85°	5	5
90°	3	2
95°	8	6
105°	8	8
115°	8	7
125°	8	7
135°	9	7
145°	11	7
155°	11	5
165°	8	3
175°	7	1
180°	7	

TEST NUMBER: P709441

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L12\_277V)

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4890.9
2.5°	4893.4
5°	4890.9
7.5°	4879.3
10°	4864.2
12.5°	4850.1
15°	4832.5
17.5°	4811.7
20°	4780.8
22.5°	4739.9
25°	4694.0
27.5°	4601.4
30°	4241.7
32.5°	3774.4
35°	3239.4
37.5°	2769.6
40°	2395.9
42.5°	2073.7
45°	1758.2
47.5°	1401.1
50°	927.1
52.5°	353.0
55°	46.7
57.5°	31.7
60°	29.2
62.5°	27.5
65°	25.9
67.5°	24.2
70°	22.5
72.5°	19.2
75°	16.7
77.5°	13.3
80°	10.0
82.5°	7.5
85°	5.0
87.5°	2.5
90°	3.4
92.5°	6.7
95°	7.5
97.5°	7.5
100°	7.5
102.5°	7.5
105°	7.5
107.5°	7.5
110°	7.5

TEST NUMBER: P709441

CATALOG NUMBER: PRLX-UHBS-1218-MV-L84050-BLAK(4000K\_L12\_277V)

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	7.5
115°	7.5
117.5°	7.5
120°	7.5
122.5°	7.5
125°	7.5
127.5°	8.4
130°	8.4
132.5°	9.2
135°	9.2
137.5°	10.0
140°	10.0
142.5°	10.0
145°	10.9
147.5°	10.9
150°	10.9
152.5°	10.9
155°	10.9
157.5°	10.9
160°	10.0
162.5°	10.0
165°	8.4
167.5°	7.5
170°	7.5
172.5°	6.7
175°	6.7
177.5°	6.7
180°	6.7

(END OF REPORT)