

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702390

Luminaire Tested: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-GFF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702390
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-14)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-GFF
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, FROSTED OUTSIDE KIT.
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 681.9 lumens
Efficiency: N/A
Efficacy: 69.6 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.63
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702390

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-GFF

Luminous Intensity Polar Plot



TEST NUMBER: P702390

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-GFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109		104	104	104		99	99	99	96
1	107	102	97	93	104	99	95	91	94	91	88		90	87	84		85	83	81	79
2	98	89	82	77	95	87	81	75	83	78	73		79	75	71		76	72	69	66
3	90	79	71	65	87	77	70	64	74	68	62		71	65	61		68	63	59	57
4	83	71	63	56	80	70	62	56	67	60	54		64	58	53		61	56	52	50
5	77	65	56	49	75	63	55	49	61	54	48		58	52	47		56	51	47	44
6	72	59	50	44	70	58	50	44	56	49	43		54	47	43		52	46	42	40
7	67	54	46	40	65	53	45	40	51	44	39		50	43	39		48	43	38	36
8	63	50	42	37	61	49	42	36	48	41	36		46	40	36		45	39	35	33
9	60	47	39	34	58	46	39	34	45	38	33		43	37	33		42	37	33	31
10	56	44	36	31	55	43	36	31	42	35	31		41	35	31		40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38440
5°	34091
10°	28416
15°	15900
20°	10625
25°	8211
30°	6638
35°	5532
40°	4932
45°	4523
50°	4124
55°	3700
60°	3301
65°	2854
70°	2444
75°	2070
80°	1759
85°	1470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4523 cd/sqm

TEST NUMBER: P702390

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-GFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	7.9
10°-20°	94.3	13.8
20°-30°	86.5	12.7
30°-40°	86.0	12.6
40°-50°	89.3	13.1
50°-60°	85.9	12.6
60°-70°	71.8	10.5
70°-80°	52.9	7.8
80°-90°	35.8	5.3
90°-100°	20.8	3.1
100°-110°	4.3	0.6
110°-120°	0.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	234.9	34.5
0°-40°	320.9	47.1
0°-60°	496.1	72.7
0°-90°	656.7	96.3
90°-120°	25.2	3.7
90°-150°	25.2	3.7
90°-180°	25.0	3.7
0°-180°	681.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	589	
5°	582	54
15°	321	94
25°	186	86
35°	136	86
45°	116	89
55°	96	86
65°	72	72
75°	50	53
85°	32	28
90°	26	14
95°	20	14
105°	3	4
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702390

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-GFF

CANDELA DISTRIBUTION (FULL):

0°	
0°	589.2
2.5°	588.3
5°	582.5
7.5°	569.2
10°	531.8
12.5°	429.4
15°	321.2
17.5°	263.8
20°	228.8
22.5°	204.7
25°	186.4
27.5°	171.4
30°	157.3
32.5°	144.8
35°	135.6
37.5°	129.0
40°	124.0
42.5°	119.8
45°	115.7
47.5°	111.5
50°	106.5
52.5°	101.5
55°	95.7
57.5°	90.7
60°	84.9
62.5°	78.2
65°	72.4
67.5°	66.6
70°	60.7
72.5°	54.9
75°	49.9
77.5°	44.9
80°	40.8
82.5°	36.6
85°	32.5
87.5°	29.1
90°	25.8
92.5°	23.3
95°	20.0
97.5°	15.0
100°	10.0
102.5°	5.8
105°	3.3
107.5°	1.7
110°	0.8

TEST NUMBER: P702390

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-GFF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)