

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702403

Luminaire Tested: 340-6C-10-D010 / 340-EU4C-1020-9050-4LBW1LI-GFC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-10-D010 / 340-EU4C-1020-9050-4LBW1LI-GFC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C
KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 748.7 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702403

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9050-4LBW1LI-GFC

Luminous Intensity Polar Plot



TEST NUMBER: P702403

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9050-4LBW1LI-GFC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	77	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42269
5°	37972
10°	32754
15°	20652
20°	14749
25°	11325
30°	9127
35°	7678
40°	6774
45°	5790
50°	4647
55°	3622
60°	2846
65°	2247
70°	1816
75°	1448
80°	1173
85°	923

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5790 cd/sqm

TEST NUMBER: P702403

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9050-4LBW1LI-GFC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.0	8.1
10°-20°	120.4	16.1
20°-30°	119.3	15.9
30°-40°	118.9	15.9
40°-50°	113.4	15.2
50°-60°	84.7	11.3
60°-70°	57.4	7.7
70°-80°	37.4	5.0
80°-90°	22.7	3.0
90°-100°	11.9	1.6
100°-110°	1.6	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.7	40.2
0°-40°	419.6	56.0
0°-60°	617.7	82.5
0°-90°	735.2	98.2
90°-120°	13.5	1.8
90°-150°	13.5	1.8
90°-180°	13.0	1.7
0°-180°	748.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	648	
5°	649	61
15°	417	120
25°	257	119
35°	188	119
45°	148	113
55°	94	85
65°	57	57
75°	35	37
85°	20	18
90°	15	9
95°	11	8
105°	1	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702403

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9050-4LBW1LI-GFC

CANDELA DISTRIBUTION (FULL):

0°	
0°	647.9
2.5°	648.8
5°	648.8
7.5°	643.7
10°	613.0
12.5°	518.5
15°	417.2
17.5°	360.1
20°	317.6
22.5°	283.5
25°	257.1
27.5°	235.0
30°	216.3
32.5°	200.1
35°	188.2
37.5°	178.8
40°	170.3
42.5°	160.9
45°	148.1
47.5°	134.5
50°	120.0
52.5°	106.4
55°	93.7
57.5°	82.6
60°	73.2
62.5°	64.7
65°	57.0
67.5°	51.1
70°	45.1
72.5°	40.0
75°	34.9
77.5°	30.7
80°	27.2
82.5°	23.8
85°	20.4
87.5°	17.9
90°	15.3
92.5°	13.6
95°	11.1
97.5°	8.5
100°	5.1
102.5°	2.6
105°	0.9
107.5°	0.0
110°	0.0

TEST NUMBER: P702403

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9050-4LBW1LI-GFC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)