

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702462

Luminaire Tested: 340-6C-15-D010 / 340-EU4C-1020-9727-4LBW1LI-CF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702462
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-12)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-15-D010 / 340-EU4C-1020-9727-4LBW1LI-CF
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL FROSTED GLASS KIT.
Light Source: 2700K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1048.6 lumens
Efficiency: N/A
Efficacy: 66.4 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.55
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702462

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9727-4LBW1LI-CF

Luminous Intensity Polar Plot



TEST NUMBER: P702462

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9727-4LBW1LI-CF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	98	107	103	99	96	98	95	93		94	92	90		90	88	87	84
2	101	94	88	83	99	92	87	82	88	84	80		85	81	78		82	79	76	74
3	94	85	78	72	92	83	77	72	80	75	70		77	73	69		75	71	67	65
4	88	77	70	64	85	76	69	64	73	67	63		71	66	62		69	64	61	59
5	82	71	63	58	80	70	63	57	68	61	56		66	60	56		64	59	55	53
6	77	66	58	52	75	65	57	52	63	56	52		61	55	51		59	54	50	49
7	73	61	53	48	71	60	53	48	58	52	47		57	51	47		55	50	47	45
8	69	57	50	44	67	56	49	44	55	48	44		53	48	44		52	47	43	42
9	65	53	46	41	64	53	46	41	52	45	41		50	45	41		49	44	40	39
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101788
5°	75100
10°	47758
15°	37958
20°	26173
25°	13157
30°	10360
35°	9028
40°	8321
45°	7377
50°	6134
55°	4863
60°	3857
65°	3051
70°	2388
75°	1908
80°	1565
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7377 cd/sqm

TEST NUMBER: P702462

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9727-4LBW1LI-CF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.3	10.4
10°-20°	209.8	20.0
20°-30°	152.3	14.5
30°-40°	139.8	13.3
40°-50°	144.2	13.7
50°-60°	113.3	10.8
60°-70°	77.0	7.3
70°-80°	49.3	4.7
80°-90°	30.5	2.9
90°-100°	17.7	1.7
100°-110°	5.3	0.5
110°-120°	0.2	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	471.4	45.0
0°-40°	611.1	58.3
0°-60°	868.6	82.8
0°-90°	1025.5	97.8
90°-120°	23.1	2.2
90°-150°	23.1	2.2
90°-180°	23.0	2.2
0°-180°	1048.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1560	
5°	1283	109
15°	767	210
25°	299	152
35°	221	140
45°	189	144
55°	126	113
65°	77	77
75°	46	49
85°	28	24
90°	21	12
95°	17	12
105°	5	5
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702462

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9727-4LBW1LI-CF

CANDELA DISTRIBUTION (FULL):

0°	
0°	1560.2
2.5°	1505.8
5°	1283.2
7.5°	1042.6
10°	893.8
12.5°	815.2
15°	766.8
17.5°	707.5
20°	563.6
22.5°	377.4
25°	298.7
27.5°	268.5
30°	245.5
32.5°	229.8
35°	221.3
37.5°	214.1
40°	209.2
42.5°	200.8
45°	188.7
47.5°	174.2
50°	158.4
52.5°	141.5
55°	125.8
57.5°	111.3
60°	99.2
62.5°	87.1
65°	77.4
67.5°	67.7
70°	59.3
72.5°	52.0
75°	46.0
77.5°	41.1
80°	36.3
82.5°	31.4
85°	27.8
87.5°	24.2
90°	20.6
92.5°	19.4
95°	16.9
97.5°	13.3
100°	9.7
102.5°	7.3
105°	4.8
107.5°	2.4
110°	1.2

TEST NUMBER: P702462

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9727-4LBW1LI-CF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)