

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P735844

Luminaire Tested: PRLX-UHBS-2436-MV-L84050-WHTE(5000K_L24_120V)

Issue Date: 1/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P735844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-243-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UHBS-2436-MV-L84050-WHTE(5000K_L24_120V)
Description: PRENTALUX LARGE HIGH BAY LUMINAIRE WITH WHITE SHADE
LIGHT LEVEL 1 - 24,0000 NOMINAL LUMENS
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22370.5 lumens
Efficiency: N/A
Efficacy: 153.4 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.25
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 1.04')
CIE Type: Direct

Input Watts (W): 145.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P735844

CATALOG NUMBER: PRLX-UHBS-2436-MV-L84050-WHTE(5000K_L24_120V)

Luminous Intensity Polar Plot





TEST NUMBER: P735844

CATALOG NUMBER: PRLX-UHBS-2436-MV-L84050-WHTE(5000K_L24_120V)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	101	98	100	98	95	96	94	92	93	91	90	88
2	103	96	90	86	100	94	89	84	91	86	83	87	84	81	84	81	79	77
3	95	86	80	74	93	85	79	74	82	77	72	79	75	71	77	73	70	68
4	88	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60
5	82	71	64	58	80	70	63	57	68	62	57	66	61	56	64	60	56	54
6	77	65	57	52	75	64	57	51	62	56	51	61	55	51	59	54	50	48
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	49	45	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	45	41	40
9	63	51	44	39	62	50	43	38	49	43	38	48	42	38	47	42	38	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50094
5°	47175
10°	45093
15°	43617
20°	42297
25°	41133
30°	37945
35°	32087
40°	25415
45°	19733
50°	13784
55°	5505
60°	4897
65°	4699
70°	4320
75°	3599
80°	2509
85°	1239

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19733 cd/sqm



TEST NUMBER: P735844

CATALOG NUMBER: PRLX-UHBS-2436-MV-L84050-WHTE(5000K_L24_120V)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1022.3	4.6
10°-20°	3069.8	13.7
20°-30°	4945.8	22.1
30°-40°	5352.9	23.9
40°-50°	4047.4	18.1
50°-60°	1657.4	7.4
60°-70°	1109.1	5.0
70°-80°	803.5	3.6
80°-90°	255.5	1.1
90°-100°	7.1	0.0
100°-110°	9.3	0.0
110°-120°	11.9	0.1
120°-130°	14.3	0.1
130°-140°	18.5	0.1
140°-150°	22.6	0.1
150°-160°	16.6	0.1
160°-170°	5.0	0.0
170°-180°	1.6	0.0
0°-30°	9037.9	40.4
0°-40°	14390.8	64.3
0°-60°	20095.6	89.8
0°-90°	22263.6	99.5
90°-120°	28.3	0.1
90°-150°	83.7	0.4
90°-180°	107.0	0.5
0°-180°	22370.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10667	
5°	10687	###
15°	10838	3070
25°	10812	4946
35°	8640	5353
45°	5278	4047
55°	1418	1657
65°	1127	1109
75°	773	803
85°	227	242
90°	8	16
95°	6	5
105°	9	9
115°	12	12
125°	16	14
135°	24	18
145°	36	23
155°	37	17
165°	16	5
175°	17	2
180°	18	

TEST NUMBER: P735844

CATALOG NUMBER: PRLX-UHBS-2436-MV-L84050-WHTE(5000K_L24_120V)

CANDELA DISTRIBUTION (FULL):

0°	
0°	10667.3
2.5°	10665.7
5°	10687.2
7.5°	10717.5
10°	10751.0
12.5°	10795.6
15°	10837.8
17.5°	10858.5
20°	10855.4
22.5°	10841.8
25°	10812.3
27.5°	10659.3
30°	10134.1
32.5°	9436.0
35°	8639.8
37.5°	7775.1
40°	6846.7
42.5°	6006.7
45°	5278.2
47.5°	4549.0
50°	3632.5
52.5°	2366.2
55°	1417.8
57.5°	1268.0
60°	1222.5
62.5°	1180.3
65°	1126.9
67.5°	1063.9
70°	985.8
72.5°	888.6
75°	773.0
77.5°	640.0
80°	501.3
82.5°	363.4
85°	227.1
87.5°	94.0
90°	8.0
92.5°	5.6
95°	6.4
97.5°	6.4
100°	7.2
102.5°	8.0
105°	8.8
107.5°	9.6
110°	10.4

TEST NUMBER: P735844

CATALOG NUMBER: PRLX-UHBS-2436-MV-L84050-WHTE(5000K_L24_120V)

CANDELA DISTRIBUTION (continued):

	0°
112.5°	11.2
115°	12.0
117.5°	12.8
120°	13.5
122.5°	14.3
125°	15.9
127.5°	17.5
130°	19.1
132.5°	21.5
135°	23.9
137.5°	26.3
140°	29.5
142.5°	31.9
145°	35.9
147.5°	40.6
150°	44.6
152.5°	41.4
155°	36.7
157.5°	28.7
160°	23.1
162.5°	17.5
165°	15.9
167.5°	15.9
170°	15.9
172.5°	16.7
175°	16.7
177.5°	17.5
180°	18.3

(END OF REPORT)