

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702447

Luminaire Tested: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-CC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702447  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-CC  
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1171.0 lumens  
Efficiency: N/A  
Efficacy: 74.1 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.71  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702447

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-CC

### Luminous Intensity Polar Plot



TEST NUMBER: P702447

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-CC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86	83	80	79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	61		68	63	60	59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56	55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53	52
10	70	60	54	50	69	60	54	50	59	54	50		58	53	50		58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	133000
5°	108595
10°	79576
15°	68717
20°	58847
25°	54399
30°	43852
35°	28465
40°	21530
45°	12013
50°	6993
55°	4641
60°	3171
65°	1976
70°	1698
75°	1286
80°	977
85°	973

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12013 cd/sqm

TEST NUMBER: P702447

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-CC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.4	12.2
10°-20°	284.7	24.3
20°-30°	336.6	28.7
30°-40°	235.5	20.1
40°-50°	109.9	9.4
50°-60°	38.1	3.3
60°-70°	14.5	1.2
70°-80°	5.9	0.5
80°-90°	1.4	0.1
90°-100°	0.9	0.1
100°-110°	0.5	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	764.6	65.3
0°-40°	1000.2	85.4
0°-60°	1148.2	98.0
0°-90°	1170.0	99.9
90°-120°	1.4	0.1
90°-150°	1.4	0.1
90°-180°	1.0	0.1
0°-180°	1171.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2039	
5°	1658	143
15°	1017	285
25°	756	337
35°	357	236
45°	130	110
55°	41	38
65°	13	14
75°	5	6
85°	1	1
90°	0	0
95°	0	1
105°	0	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P702447

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-CC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2038.6
2.5°	1937.8
5°	1658.2
7.5°	1382.5
10°	1201.2
12.5°	1094.0
15°	1017.4
17.5°	948.5
20°	847.6
22.5°	772.3
25°	755.7
27.5°	691.9
30°	582.1
32.5°	458.3
35°	357.4
37.5°	292.3
40°	252.8
42.5°	196.6
45°	130.2
47.5°	90.6
50°	68.9
52.5°	52.3
55°	40.8
57.5°	31.9
60°	24.3
62.5°	17.9
65°	12.8
67.5°	11.5
70°	8.9
72.5°	7.7
75°	5.1
77.5°	3.8
80°	2.6
82.5°	1.3
85°	1.3
87.5°	1.3
90°	0.0
92.5°	0.0
95°	0.0
97.5°	1.3
100°	1.3
102.5°	1.3
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P702447

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-CC

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)