

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702451

Luminaire Tested: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GCC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-16)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GCC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1267.8 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.89
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702451

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GCC

Luminous Intensity Polar Plot



TEST NUMBER: P702451

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GCC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90	87	85	83
3	100	93	87	83	98	91	86	82	88	84	81		86	82	79		84	81	78	76
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	74	71	70
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73	69	66	64
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61	59
7	79	69	62	58	78	68	62	57	67	61	57		66	60	57		64	60	56	55
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61	56	52	51
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57	52	49	48
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54	49	46	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84617
5°	81345
10°	77377
15°	69751
20°	63013
25°	53758
30°	45870
35°	33044
40°	25226
45°	16958
50°	10495
55°	7553
60°	5493
65°	3751
70°	3166
75°	2571
80°	2405
85°	1946

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16958 cd/sqm

TEST NUMBER: P702451

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GCC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	9.2
10°-20°	291.3	23.0
20°-30°	343.4	27.1
30°-40°	266.9	21.1
40°-50°	146.4	11.6
50°-60°	61.0	4.8
60°-70°	25.8	2.0
70°-80°	11.1	0.9
80°-90°	3.1	0.2
90°-100°	1.4	0.1
100°-110°	0.9	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	751.0	59.2
0°-40°	1017.9	80.3
0°-60°	1225.4	96.7
0°-90°	1265.5	99.8
90°-120°	2.3	0.2
90°-150°	2.3	0.2
90°-180°	2.0	0.2
0°-180°	1267.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1297	
5°	1242	116
15°	1033	291
25°	747	343
35°	415	267
45°	184	146
55°	66	61
65°	24	26
75°	10	11
85°	3	3
90°	1	1
95°	1	1
105°	1	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702451

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GCC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1297.0
2.5°	1282.9
5°	1242.1
7.5°	1205.0
10°	1168.0
12.5°	1100.4
15°	1032.7
17.5°	989.3
20°	907.6
22.5°	809.3
25°	746.8
27.5°	685.5
30°	608.9
32.5°	515.7
35°	414.9
37.5°	342.1
40°	296.2
42.5°	251.5
45°	183.8
47.5°	132.8
50°	103.4
52.5°	81.7
55°	66.4
57.5°	53.6
60°	42.1
62.5°	30.6
65°	24.3
67.5°	20.4
70°	16.6
72.5°	12.8
75°	10.2
77.5°	7.7
80°	6.4
82.5°	3.8
85°	2.6
87.5°	1.3
90°	1.3
92.5°	1.3
95°	1.3
97.5°	1.3
100°	1.3
102.5°	1.3
105°	1.3
107.5°	0.0
110°	0.0

TEST NUMBER: P702451

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GCC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)