

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702452

Luminaire Tested: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702452
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C
KIT.
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1122.5 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702452

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

Luminous Intensity Polar Plot



TEST NUMBER: P702452

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	76	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63375
5°	56928
10°	49110
15°	30964
20°	22110
25°	16981
30°	13681
35°	11508
40°	10154
45°	8683
50°	6971
55°	5427
60°	4269
65°	3370
70°	2726
75°	2170
80°	1759
85°	1384

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8683 cd/sqm

TEST NUMBER: P702452

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	8.1
10°-20°	180.5	16.1
20°-30°	178.8	15.9
30°-40°	178.2	15.9
40°-50°	170.1	15.2
50°-60°	126.9	11.3
60°-70°	86.1	7.7
70°-80°	56.1	5.0
80°-90°	34.1	3.0
90°-100°	17.8	1.6
100°-110°	2.4	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	450.8	40.2
0°-40°	629.1	56.0
0°-60°	926.1	82.5
0°-90°	1102.3	98.2
90°-120°	20.2	1.8
90°-150°	20.2	1.8
90°-180°	20.0	1.8
0°-180°	1122.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	971	
5°	973	91
15°	626	181
25°	386	179
35°	282	178
45°	222	170
55°	140	127
65°	86	86
75°	52	56
85°	31	27
90°	23	13
95°	17	12
105°	1	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702452

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

CANDELA DISTRIBUTION (FULL):

0°	
0°	971.4
2.5°	972.7
5°	972.7
7.5°	965.1
10°	919.1
12.5°	777.4
15°	625.5
17.5°	540.0
20°	476.1
22.5°	425.1
25°	385.5
27.5°	352.3
30°	324.2
32.5°	300.0
35°	282.1
37.5°	268.1
40°	255.3
42.5°	241.3
45°	222.1
47.5°	201.7
50°	180.0
52.5°	159.6
55°	140.4
57.5°	123.8
60°	109.8
62.5°	97.0
65°	85.5
67.5°	76.6
70°	67.7
72.5°	60.0
75°	52.3
77.5°	46.0
80°	40.8
82.5°	35.7
85°	30.6
87.5°	26.8
90°	23.0
92.5°	20.4
95°	16.6
97.5°	12.8
100°	7.7
102.5°	3.8
105°	1.3
107.5°	0.0
110°	0.0

TEST NUMBER: P702452

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)