

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219658

Luminaire Tested: **MRZ-1-REC-X-4-L27-80-NFL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14873)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-4-L27-80-NFL-UNV-X-STD-SFL
Description: MRZ INTEGRAL LED DOWNLIGHT
25 DEGREE NARROW FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL 4
Light Source: (1) 2700K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1504.5 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.4
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219658

CATALOG NUMBER: MRZ-1-REC-X-4-L27-80-NFL-UNV-X-STD-SFL

Luminous Intensity Polar Plot





TEST NUMBER: P219658

CATALOG NUMBER: MRZ-1-REC-X-4-L27-80-NFL-UNV-X-STD-SFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	95	98	95	93	96	94	92	94	92	90	89
4	103	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	85	90	87	85	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80
7	94	88	83	80	93	87	83	80	86	82	80	85	82	79	84	81	79	78
8	92	85	80	77	91	84	80	77	83	80	77	82	79	77	82	79	76	75
9	89	82	78	75	88	82	78	75	81	77	75	80	77	74	79	76	74	73
10	87	80	76	73	86	79	75	73	79	75	73	78	75	72	77	74	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3372841
5°	3076829
10°	2213527
15°	1099565
20°	447967
25°	231254
30°	135818
35°	78782
40°	49657
45°	33771
50°	22029
55°	13849
60°	8881
65°	8406
70°	5193
75°	3431
80°	5114
85°	0



TEST NUMBER: P219658

CATALOG NUMBER: MRZ-1-REC-X-4-L27-80-NFL-UNV-X-STD-SFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	535.4	35.6
10°-20°	611.8	40.7
20°-30°	208.2	13.8
30°-40°	86.7	5.8
40°-50°	37.8	2.5
50°-60°	15.3	1.0
60°-70°	6.4	0.4
70°-80°	2.6	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1355.3	90.1
0°-40°	1442.0	95.8
0°-60°	1495.2	99.4
0°-90°	1504.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1504.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6836	
5°	6212	535
15°	2153	612
25°	425	208
35°	131	87
45°	48	38
55°	16	15
65°	7	6
75°	2	3
85°	0	0
90°	0	

TEST NUMBER: P219658

CATALOG NUMBER: MRZ-1-REC-X-4-L27-80-NFL-UNV-X-STD-SFL

CANDELA DISTRIBUTION (FULL):

	0°
0°	6836.2
2.5°	6685.7
5°	6212.5
7.5°	5436.4
10°	4418.3
12.5°	3265.8
15°	2152.7
17.5°	1330.0
20°	853.2
22.5°	578.9
25°	424.8
27.5°	317.3
30°	238.4
32.5°	177.4
35°	130.8
37.5°	98.6
40°	77.1
42.5°	59.1
45°	48.4
47.5°	37.6
50°	28.7
52.5°	21.5
55°	16.1
57.5°	12.5
60°	9.0
62.5°	7.2
65°	7.2
67.5°	5.4
70°	3.6
72.5°	3.6
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)