

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219794

Luminaire Tested: **MRZ-1-REC-X-1H-L27-97-FL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219794
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14878)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-1H-L27-97-FL-UNV-X-STD-SFL
Description: MRZ INTEGRAL LED DOWNLIGHT
40 DEGREE FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL 1
Light Source: (1) 2700K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 445.1 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 6.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219794

CATALOG NUMBER: MRZ-1-REC-X-1H-L27-97-FL-UNV-X-STD-SFL

Luminous Intensity Polar Plot





TEST NUMBER: P219794

CATALOG NUMBER: MRZ-1-REC-X-1H-L27-97-FL-UNV-X-STD-SFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94
2	109	105	101	98	107	103	99	97	100	97	95	97	94	93	94	92	91	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	88	85	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79
5	95	88	83	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75
6	91	83	78	74	90	83	78	74	81	77	73	80	76	73	79	75	73	71
7	88	79	74	70	86	79	74	70	77	73	70	76	72	69	75	72	69	68
8	84	76	70	67	83	75	70	66	74	69	66	73	69	66	72	68	66	64
9	81	72	67	63	80	72	67	63	71	66	63	70	66	63	69	65	63	61
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	391793
5°	391952
10°	373438
15°	315971
20°	231492
25°	148562
30°	84772
35°	45113
40°	24152
45°	13815
50°	8597
55°	6021
60°	4243
65°	3152
70°	2308
75°	2097
80°	1421
85°	0



TEST NUMBER: P219794

CATALOG NUMBER: MRZ-1-REC-X-1H-L27-97-FL-UNV-X-STD-SFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.2	16.7
10°-20°	168.2	37.8
20°-30°	126.2	28.3
30°-40°	50.1	11.3
40°-50°	16.3	3.7
50°-60°	6.4	1.4
60°-70°	2.7	0.6
70°-80°	1.0	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	368.5	82.8
0°-40°	418.6	94.0
0°-60°	441.3	99.2
0°-90°	445.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	445.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	794	
5°	791	74
15°	619	168
25°	273	126
35°	75	50
45°	20	16
55°	7	6
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P219794

CATALOG NUMBER: MRZ-1-REC-X-1H-L27-97-FL-UNV-X-STD-SFL

CANDELA DISTRIBUTION (FULL):

0°	
0°	794.1
2.5°	795.1
5°	791.4
7.5°	778.0
10°	745.4
12.5°	691.9
15°	618.6
17.5°	532.4
20°	440.9
22.5°	352.6
25°	272.9
27.5°	204.4
30°	148.8
32.5°	106.5
35°	74.9
37.5°	53.0
40°	37.5
42.5°	27.3
45°	19.8
47.5°	14.4
50°	11.2
52.5°	8.6
55°	7.0
57.5°	5.4
60°	4.3
62.5°	3.2
65°	2.7
67.5°	2.1
70°	1.6
72.5°	1.1
75°	1.1
77.5°	0.5
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)