

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P14880

Luminaire Tested: **MRZ-1-REC-X-3-L27-97-WFL-UNV-X-STD**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P14880  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-3-L27-97-WFL-UNV-X-STD  
Description: MRZ INTEGRAL LED DOWNLIGHT  
55 DEGREE WIDE FLOOD OPTIC, LIGHT LEVEL 3  
Light Source: (1) 2700K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 816.9 lumens  
Efficiency: N/A  
Efficacy: 68.7 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.91  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P14880

CATALOG NUMBER: MRZ-1-REC-X-3-L27-97-WFL-UNV-X-STD

### Luminous Intensity Polar Plot





TEST NUMBER: P14880

CATALOG NUMBER: MRZ-1-REC-X-3-L27-97-WFL-UNV-X-STD

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	94	86	81	76	84	79	76		82	78	75		80	77	74	72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75	71	68	67
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71	66	63	62
7	81	71	64	60	79	70	64	60	69	63	59		68	63	59		66	62	59	57
8	76	66	60	56	75	66	60	56	65	59	55		64	59	55		63	58	55	53
9	73	62	56	52	71	62	56	52	61	55	52		60	55	51		59	55	51	50
10	69	59	53	49	68	58	52	48	57	52	48		57	52	48		56	51	48	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	404571
5°	406612
10°	395282
15°	361635
20°	323427
25°	290701
30°	239276
35°	170452
40°	112711
45°	71868
50°	44519
55°	27526
60°	15788
65°	8172
70°	4328
75°	3813
80°	0
85°	0



TEST NUMBER: P14880

CATALOG NUMBER: MRZ-1-REC-X-3-L27-97-WFL-UNV-X-STD

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.4	9.5
10°-20°	197.4	24.2
20°-30°	241.9	29.6
30°-40°	178.4	21.8
40°-50°	82.5	10.1
50°-60°	29.9	3.7
60°-70°	7.7	0.9
70°-80°	1.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	516.6	63.2
0°-40°	695.1	85.1
0°-60°	807.5	98.8
0°-90°	816.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	816.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	820	
5°	821	77
15°	708	197
25°	534	242
35°	283	178
45°	103	83
55°	32	30
65°	7	8
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P14880

CATALOG NUMBER: MRZ-1-REC-X-3-L27-97-WFL-UNV-X-STD

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	820
2.5°	819
5°	821
7.5°	812
10°	789
12.5°	754
15°	708
17.5°	658
20°	616
22.5°	579
25°	534
27.5°	482
30°	420
32.5°	351
35°	283
37.5°	224
40°	175
42.5°	135
45°	103
47.5°	78
50°	58
52.5°	43
55°	32
57.5°	23
60°	16
62.5°	11
65°	7
67.5°	4
70°	3
72.5°	2
75°	2
77.5°	1
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)