

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219853

Luminaire Tested: **MRZ-1-REC-X-1H-L30-80-WFL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219853  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14881)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-1H-L30-80-WFL-UNV-X-STD-HEX  
Description: MRZ INTEGRAL LED DOWNLIGHT  
55 DEGREE WIDE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 1  
Light Source: (1) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 289.0 lumens  
Efficiency: N/A  
Efficacy: 42.5 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.67  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 6.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219853

CATALOG NUMBER: MRZ-1-REC-X-1H-L30-80-WFL-UNV-X-STD-HEX

### Luminous Intensity Polar Plot





TEST NUMBER: P219853

CATALOG NUMBER: MRZ-1-REC-X-1H-L30-80-WFL-UNV-X-STD-HEX

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	81	78	84	80	78	83	79	77	76
6	92	84	78	75	90	83	78	74	82	77	74	80	76	73	79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62
10	78	69	64	61	77	69	64	60	68	63	60	67	63	60	67	63	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	279352
5°	264223
10°	233662
15°	189194
20°	144072
25°	106645
30°	68593
35°	36259
40°	15715
45°	5861
50°	2303
55°	1290
60°	789
65°	934
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P219853

CATALOG NUMBER: MRZ-1-REC-X-1H-L30-80-WFL-UNV-X-STD-HEX

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.8	16.9
10°-20°	102.0	35.3
20°-30°	88.9	30.8
30°-40°	39.4	13.6
40°-50°	7.7	2.7
50°-60°	1.6	0.6
60°-70°	0.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	239.8	83.0
0°-40°	279.2	96.6
0°-60°	288.5	99.8
0°-90°	289.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	289.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	566	
5°	534	49
15°	370	102
25°	196	89
35°	60	39
45°	8	8
55°	2	2
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P219853

CATALOG NUMBER: MRZ-1-REC-X-1H-L30-80-WFL-UNV-X-STD-HEX

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	566.2
2.5°	554.8
5°	533.5
7.5°	504.5
10°	466.4
12.5°	419.9
15°	370.4
17.5°	318.6
20°	274.4
22.5°	235.5
25°	195.9
27.5°	157.8
30°	120.4
32.5°	86.9
35°	60.2
37.5°	38.9
40°	24.4
42.5°	13.7
45°	8.4
47.5°	5.3
50°	3.0
52.5°	2.3
55°	1.5
57.5°	1.5
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)