

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702550

Luminaire Tested: 340-6C-25-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702550
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-25-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C
KIT.
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1793.4 lumens
Efficiency: N/A
Efficacy: 56.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702550

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

Luminous Intensity Polar Plot



TEST NUMBER: P702550

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	76	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101260
5°	90955
10°	78461
15°	49473
20°	35326
25°	27130
30°	21859
35°	18386
40°	16224
45°	13875
50°	11138
55°	8671
60°	6820
65°	5384
70°	4353
75°	3468
80°	2816
85°	2212

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13875 cd/sqm

TEST NUMBER: P702550

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.1	8.1
10°-20°	288.5	16.1
20°-30°	285.7	15.9
30°-40°	284.7	15.9
40°-50°	271.8	15.2
50°-60°	202.8	11.3
60°-70°	137.5	7.7
70°-80°	89.6	5.0
80°-90°	54.5	3.0
90°-100°	28.4	1.6
100°-110°	3.8	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	720.3	40.2
0°-40°	1005.0	56.0
0°-60°	1479.6	82.5
0°-90°	1761.2	98.2
90°-120°	32.2	1.8
90°-150°	32.2	1.8
90°-180°	32.0	1.8
0°-180°	1793.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1552	
5°	1554	146
15°	999	288
25°	616	286
35°	451	285
45°	355	272
55°	224	203
65°	137	137
75°	84	90
85°	49	44
90°	37	20
95°	26	19
105°	2	4
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702550

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1552.1
2.5°	1554.1
5°	1554.1
7.5°	1541.9
10°	1468.4
12.5°	1242.1
15°	999.4
17.5°	862.7
20°	760.7
22.5°	679.2
25°	615.9
27.5°	562.9
30°	518.0
32.5°	479.3
35°	450.7
37.5°	428.3
40°	407.9
42.5°	385.5
45°	354.9
47.5°	322.2
50°	287.6
52.5°	254.9
55°	224.3
57.5°	197.8
60°	175.4
62.5°	155.0
65°	136.6
67.5°	122.4
70°	108.1
72.5°	95.9
75°	83.6
77.5°	73.4
80°	65.3
82.5°	57.1
85°	48.9
87.5°	42.8
90°	36.7
92.5°	32.6
95°	26.5
97.5°	20.4
100°	12.2
102.5°	6.1
105°	2.0
107.5°	0.0
110°	0.0

TEST NUMBER: P702550

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)