

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P226126

Luminaire Tested: **MRZ-1-REC-X-1-L30-80-WFL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P226126  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14881)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-1-L30-80-WFL-UNV-X-STD-HEX  
Description: MRZ INTEGRAL LED DOWNLIGHT  
55 DEGREE WIDE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 1  
Light Source: (1) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 258.0 lumens  
Efficiency: N/A  
Efficacy: 47.8 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.67  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 5.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P226126

CATALOG NUMBER: MRZ-1-REC-X-1-L30-80-WFL-UNV-X-STD-HEX

### Luminous Intensity Polar Plot





TEST NUMBER: P226126

CATALOG NUMBER: MRZ-1-REC-X-1-L30-80-WFL-UNV-X-STD-HEX

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	81	78	84	80	78	83	79	77	76
6	92	84	78	75	90	83	78	74	82	77	74	80	76	73	79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62
10	78	69	64	61	77	69	64	60	68	63	60	67	63	60	67	63	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	249354
5°	235845
10°	208562
15°	168916
20°	128636
25°	95213
30°	61243
35°	32344
40°	14041
45°	5233
50°	2072
55°	1118
60°	691
65°	817
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P226126

CATALOG NUMBER: MRZ-1-REC-X-1-L30-80-WFL-UNV-X-STD-HEX

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	43.6	16.9
10°-20°	91.1	35.3
20°-30°	79.4	30.8
30°-40°	35.2	13.6
40°-50°	6.9	2.7
50°-60°	1.4	0.6
60°-70°	0.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	214.0	83.0
0°-40°	249.2	96.6
0°-60°	257.6	99.8
0°-90°	258.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	258.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	505	
5°	476	44
15°	331	91
25°	175	79
35°	54	35
45°	8	7
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P226126

CATALOG NUMBER: MRZ-1-REC-X-1-L30-80-WFL-UNV-X-STD-HEX

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	505.4
2.5°	495.3
5°	476.2
7.5°	450.4
10°	416.3
12.5°	374.8
15°	330.7
17.5°	284.4
20°	245.0
22.5°	210.2
25°	174.9
27.5°	140.9
30°	107.5
32.5°	77.6
35°	53.7
37.5°	34.7
40°	21.8
42.5°	12.2
45°	7.5
47.5°	4.7
50°	2.7
52.5°	2.1
55°	1.3
57.5°	1.3
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)