

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702557

Luminaire Tested: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-GFC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702557  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-GFC  
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C  
KIT.  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1817.8 lumens  
Efficiency: N/A  
Efficacy: 57.7 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74  
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')  
CIE Type: Direct

Input Watts (W): 31.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702557

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-GFC

### Luminous Intensity Polar Plot



TEST NUMBER: P702557

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-GFC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	76	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	102630
5°	92190
10°	79524
15°	50141
20°	35805
25°	27500
30°	22158
35°	18635
40°	16443
45°	14062
50°	11289
55°	8791
60°	6914
65°	5459
70°	4414
75°	3518
80°	2850
85°	2244

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14062 cd/sqm

TEST NUMBER: P702557

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-GFC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.1	8.1
10°-20°	292.4	16.1
20°-30°	289.6	15.9
30°-40°	288.6	15.9
40°-50°	275.4	15.2
50°-60°	205.6	11.3
60°-70°	139.4	7.7
70°-80°	90.9	5.0
80°-90°	55.2	3.0
90°-100°	28.8	1.6
100°-110°	3.9	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	730.1	40.2
0°-40°	1018.7	56.0
0°-60°	1499.7	82.5
0°-90°	1785.1	98.2
90°-120°	32.7	1.8
90°-150°	32.7	1.8
90°-180°	33.0	1.8
0°-180°	1817.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1573	
5°	1575	148
15°	1013	292
25°	624	290
35°	457	289
45°	360	275
55°	227	206
65°	138	139
75°	85	91
85°	50	44
90°	37	21
95°	27	19
105°	2	4
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702557

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-GFC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1573.1
2.5°	1575.2
5°	1575.2
7.5°	1562.8
10°	1488.3
12.5°	1258.9
15°	1012.9
17.5°	874.4
20°	771.0
22.5°	688.4
25°	624.3
27.5°	570.5
30°	525.1
32.5°	485.8
35°	456.8
37.5°	434.1
40°	413.4
42.5°	390.7
45°	359.7
47.5°	326.6
50°	291.5
52.5°	258.4
55°	227.4
57.5°	200.5
60°	177.8
62.5°	157.1
65°	138.5
67.5°	124.0
70°	109.6
72.5°	97.2
75°	84.8
77.5°	74.4
80°	66.1
82.5°	57.9
85°	49.6
87.5°	43.4
90°	37.2
92.5°	33.1
95°	26.9
97.5°	20.7
100°	12.4
102.5°	6.2
105°	2.1
107.5°	0.0
110°	0.0

TEST NUMBER: P702557

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9035-4LBW1LI-GFC

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)