

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702564

Luminaire Tested: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702564
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C
KIT.
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1821.6 lumens
Efficiency: N/A
Efficacy: 57.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702564

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFC

Luminous Intensity Polar Plot



TEST NUMBER: P702564

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	76	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102852
5°	92383
10°	79695
15°	50250
20°	35884
25°	27557
30°	22205
35°	18676
40°	16479
45°	14093
50°	11312
55°	8810
60°	6929
65°	5471
70°	4422
75°	3522
80°	2859
85°	2249

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14093 cd/sqm

TEST NUMBER: P702564

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.4	8.1
10°-20°	293.0	16.1
20°-30°	290.2	15.9
30°-40°	289.2	15.9
40°-50°	276.0	15.2
50°-60°	206.0	11.3
60°-70°	139.7	7.7
70°-80°	91.1	5.0
80°-90°	55.3	3.0
90°-100°	28.8	1.6
100°-110°	3.9	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	731.7	40.2
0°-40°	1020.8	56.0
0°-60°	1502.9	82.5
0°-90°	1788.9	98.2
90°-120°	32.7	1.8
90°-150°	32.7	1.8
90°-180°	33.0	1.8
0°-180°	1821.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1576	
5°	1578	148
15°	1015	293
25°	626	290
35°	458	289
45°	360	276
55°	228	206
65°	139	140
75°	85	91
85°	50	44
90°	37	21
95°	27	19
105°	2	4
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702564

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1576.5
2.5°	1578.5
5°	1578.5
7.5°	1566.1
10°	1491.5
12.5°	1261.6
15°	1015.1
17.5°	876.3
20°	772.7
22.5°	689.8
25°	625.6
27.5°	571.8
30°	526.2
32.5°	486.8
35°	457.8
37.5°	435.0
40°	414.3
42.5°	391.5
45°	360.5
47.5°	327.3
50°	292.1
52.5°	258.9
55°	227.9
57.5°	200.9
60°	178.2
62.5°	157.4
65°	138.8
67.5°	124.3
70°	109.8
72.5°	97.4
75°	84.9
77.5°	74.6
80°	66.3
82.5°	58.0
85°	49.7
87.5°	43.5
90°	37.3
92.5°	33.1
95°	26.9
97.5°	20.7
100°	12.4
102.5°	6.2
105°	2.1
107.5°	0.0
110°	0.0

TEST NUMBER: P702564

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)