

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702565

Luminaire Tested: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFF

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702565  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFF  
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, FROSTED OUTSIDE KIT.  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1697.6 lumens  
Efficiency: N/A  
Efficacy: 53.9 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.63  
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')  
CIE Type: Direct

Input Watts (W): 31.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702565

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFF

### Luminous Intensity Polar Plot



TEST NUMBER: P702565

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFF

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109		104	104	104		99	99	99	96
1	107	102	97	93	104	99	95	91	94	91	88		90	87	84		85	83	81	79
2	98	89	82	77	95	87	81	75	83	78	73		79	75	71		76	72	69	66
3	90	79	71	65	87	77	70	64	74	68	62		71	65	61		68	63	59	57
4	83	71	63	56	80	70	62	56	67	60	54		64	58	53		61	56	52	50
5	77	65	56	49	75	63	55	49	61	54	48		58	52	47		56	51	47	44
6	72	59	50	44	70	58	50	44	56	49	43		54	47	43		52	46	42	40
7	67	54	46	40	65	53	45	40	51	44	39		50	43	39		48	43	38	36
8	63	50	42	37	61	49	42	36	48	41	36		46	40	36		45	39	35	33
9	60	47	39	34	58	46	39	34	45	38	33		43	37	33		42	37	33	31
10	56	44	36	31	55	43	36	31	42	35	31		41	35	31		40	34	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	95688
5°	84868
10°	70729
15°	39582
20°	26456
25°	20439
30°	16521
35°	13776
40°	12278
45°	11259
50°	10270
55°	9208
60°	8216
65°	7102
70°	6089
75°	5157
80°	4377
85°	3656

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11259 cd/sqm

TEST NUMBER: P702565

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFF

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.8	7.9
10°-20°	234.7	13.8
20°-30°	215.3	12.7
30°-40°	214.1	12.6
40°-50°	222.4	13.1
50°-60°	213.7	12.6
60°-70°	178.8	10.5
70°-80°	131.8	7.8
80°-90°	89.2	5.3
90°-100°	51.8	3.0
100°-110°	10.8	0.6
110°-120°	0.3	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.9	34.5
0°-40°	798.9	47.1
0°-60°	1235.0	72.7
0°-90°	1634.8	96.3
90°-120°	62.8	3.7
90°-150°	62.8	3.7
90°-180°	63.0	3.7
0°-180°	1697.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1467	
5°	1450	135
15°	800	235
25°	464	215
35°	338	214
45°	288	222
55°	238	214
65°	180	179
75°	124	132
85°	81	70
90°	64	35
95°	50	35
105°	8	11
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702565

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFF

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1466.7
2.5°	1464.6
5°	1450.1
7.5°	1417.0
10°	1323.7
12.5°	1068.9
15°	799.6
17.5°	656.7
20°	569.7
22.5°	509.6
25°	464.0
27.5°	426.7
30°	391.5
32.5°	360.5
35°	337.7
37.5°	321.1
40°	308.7
42.5°	298.3
45°	288.0
47.5°	277.6
50°	265.2
52.5°	252.7
55°	238.2
57.5°	225.8
60°	211.3
62.5°	194.7
65°	180.2
67.5°	165.7
70°	151.2
72.5°	136.7
75°	124.3
77.5°	111.9
80°	101.5
82.5°	91.1
85°	80.8
87.5°	72.5
90°	64.2
92.5°	58.0
95°	49.7
97.5°	37.3
100°	24.9
102.5°	14.5
105°	8.3
107.5°	4.1
110°	2.1

TEST NUMBER: P702565

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9040-4LBW1LI-GFF

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)