

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702568

Luminaire Tested: 340-6C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-CQ

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702568
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-13)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-CQ
Description: FARALLON 6" LED GLASS DOWNLIGHT CYLINDRICAL FROSTED, QUADRATE ETCHED GLASS KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1810.5 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.54
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702568

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-CQ

Luminous Intensity Polar Plot



TEST NUMBER: P702568

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-CQ

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	110	105	102	98	107	103	100	97	98	96	93		94	92	90		90	89	87	85
2	102	95	89	84	99	93	87	83	89	84	81		85	82	78		82	79	76	74
3	95	86	79	73	92	84	78	72	81	75	71		78	73	70		75	71	68	66
4	88	78	71	65	86	77	70	64	74	68	63		72	67	62		69	65	61	59
5	83	72	64	58	81	71	63	58	68	62	57		66	61	57		64	60	56	54
6	78	66	59	53	76	65	58	53	63	57	52		62	56	52		60	55	51	49
7	73	62	54	49	71	61	54	49	59	53	48		58	52	48		56	51	47	46
8	69	58	50	45	68	57	50	45	55	49	45		54	48	44		53	48	44	42
9	66	54	47	42	64	53	47	42	52	46	42		51	45	41		50	45	41	40
10	62	51	44	40	61	50	44	39	49	43	39		48	43	39		47	42	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	180651
5°	129769
10°	82335
15°	65917
20°	45348
25°	25139
30°	19711
35°	16554
40°	14545
45°	12064
50°	9906
55°	7844
60°	6245
65°	4915
70°	3914
75°	3157
80°	2553
85°	2104

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12064 cd/sqm

TEST NUMBER: P702568

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-CQ

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	10.5
10°-20°	363.7	20.1
20°-30°	282.3	15.6
30°-40°	256.8	14.2
40°-50°	238.2	13.2
50°-60°	183.4	10.1
60°-70°	125.5	6.9
70°-80°	81.5	4.5
80°-90°	50.7	2.8
90°-100°	29.4	1.6
100°-110°	9.3	0.5
110°-120°	0.3	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	835.4	46.1
0°-40°	1092.2	60.3
0°-60°	1513.9	83.6
0°-90°	1771.5	97.8
90°-120°	39.0	2.2
90°-150°	39.0	2.2
90°-180°	39.0	2.2
0°-180°	1810.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2769	
5°	2217	190
15°	1332	364
25°	571	282
35°	406	257
45°	309	238
55°	203	183
65°	125	125
75°	76	81
85°	46	41
90°	34	19
95°	28	20
105°	8	9
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702568

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-CQ

CANDELA DISTRIBUTION (FULL):

0°	
0°	2769.0
2.5°	2646.4
5°	2217.3
7.5°	1803.0
10°	1540.9
12.5°	1412.0
15°	1331.6
17.5°	1228.1
20°	976.5
22.5°	682.7
25°	570.7
27.5°	515.7
30°	467.1
32.5°	429.1
35°	405.8
37.5°	391.0
40°	365.7
42.5°	336.1
45°	308.6
47.5°	281.1
50°	255.8
52.5°	228.3
55°	202.9
57.5°	181.8
60°	160.6
62.5°	141.6
65°	124.7
67.5°	112.0
70°	97.2
72.5°	86.7
75°	76.1
77.5°	67.6
80°	59.2
82.5°	52.8
85°	46.5
87.5°	40.2
90°	33.8
92.5°	31.7
95°	27.5
97.5°	23.3
100°	16.9
102.5°	12.7
105°	8.5
107.5°	4.2
110°	2.1

TEST NUMBER: P702568

CATALOG NUMBER: 340-6C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-CQ

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)