

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219872

Luminaire Tested: **MRZ-1-REC-X-3-L30-97-WFL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219872  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14881)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-3-L30-97-WFL-UNV-X-STD-HEX  
Description: MRZ INTEGRAL LED DOWNLIGHT  
55 DEGREE WIDE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 3  
Light Source: (1) 3000K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 414.6 lumens  
Efficiency: N/A  
Efficacy: 34.3 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.67  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 12.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219872

CATALOG NUMBER: MRZ-1-REC-X-3-L30-97-WFL-UNV-X-STD-HEX

### Luminous Intensity Polar Plot





TEST NUMBER: P219872

CATALOG NUMBER: MRZ-1-REC-X-3-L30-97-WFL-UNV-X-STD-HEX

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	81	78	84	80	78	83	79	77	76
6	92	84	78	75	90	83	78	74	82	77	74	80	76	73	79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62
10	78	69	64	61	77	69	64	60	68	63	60	67	63	60	67	63	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	400772
5°	379026
10°	335213
15°	271380
20°	206657
25°	152972
30°	98388
35°	52039
40°	22542
45°	8373
50°	3377
55°	1892
60°	1085
65°	1284
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P219872

CATALOG NUMBER: MRZ-1-REC-X-3-L30-97-WFL-UNV-X-STD-HEX

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.1	16.9
10°-20°	146.3	35.3
20°-30°	127.6	30.8
30°-40°	56.5	13.6
40°-50°	11.1	2.7
50°-60°	2.3	0.6
60°-70°	0.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	343.9	83.0
0°-40°	400.5	96.6
0°-60°	413.9	99.8
0°-90°	414.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	414.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	812	
5°	765	70
15°	531	146
25°	281	128
35°	86	57
45°	12	11
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P219872

CATALOG NUMBER: MRZ-1-REC-X-3-L30-97-WFL-UNV-X-STD-HEX

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	812.3
2.5°	795.9
5°	765.3
7.5°	723.7
10°	669.1
12.5°	602.4
15°	531.3
17.5°	457.0
20°	393.6
22.5°	337.8
25°	281.0
27.5°	226.3
30°	172.7
32.5°	124.6
35°	86.4
37.5°	55.8
40°	35.0
42.5°	19.7
45°	12.0
47.5°	7.7
50°	4.4
52.5°	3.3
55°	2.2
57.5°	2.2
60°	1.1
62.5°	1.1
65°	1.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)