

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219792

Luminaire Tested: **MRZ-1-REC-X-1H-L35-80-FL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219792  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14878)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-1H-L35-80-FL-UNV-X-STD-SFL  
Description: MRZ INTEGRAL LED DOWNLIGHT  
40 DEGREE FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL 1  
Light Source: (1) 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 668.0 lumens  
Efficiency: N/A  
Efficacy: 98.2 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.66  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 6.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219792

CATALOG NUMBER: MRZ-1-REC-X-1H-L35-80-FL-UNV-X-STD-SFL

### Luminous Intensity Polar Plot





TEST NUMBER: P219792

CATALOG NUMBER: MRZ-1-REC-X-1H-L35-80-FL-UNV-X-STD-SFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94
2	109	105	101	98	107	103	99	97	100	97	95	97	94	93	94	92	91	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	88	85	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79
5	95	88	83	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75
6	91	83	78	74	90	83	78	74	81	77	73	80	76	73	79	75	73	71
7	88	79	74	70	86	79	74	70	77	73	70	76	72	69	75	72	69	68
8	84	76	70	67	83	75	70	66	74	69	66	73	69	66	72	68	66	64
9	81	72	67	63	80	72	67	63	71	66	63	70	66	63	69	65	63	61
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	588108
5°	588374
10°	560559
15°	474263
20°	347526
25°	222980
30°	127215
35°	67759
40°	36196
45°	20723
50°	12972
55°	8946
60°	6315
65°	4670
70°	3462
75°	3050
80°	2273
85°	0



TEST NUMBER: P219792

CATALOG NUMBER: MRZ-1-REC-X-1H-L35-80-FL-UNV-X-STD-SFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.3	16.7
10°-20°	252.4	37.8
20°-30°	189.4	28.3
30°-40°	75.2	11.3
40°-50°	24.6	3.7
50°-60°	9.5	1.4
60°-70°	4.0	0.6
70°-80°	1.5	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.1	82.8
0°-40°	628.3	94.1
0°-60°	662.4	99.2
0°-90°	668.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	668.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1192	
5°	1188	111
15°	928	252
25°	410	189
35°	112	75
45°	30	25
55°	10	10
65°	4	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P219792

CATALOG NUMBER: MRZ-1-REC-X-1H-L35-80-FL-UNV-X-STD-SFL

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1192.0
2.5°	1193.6
5°	1188.0
7.5°	1167.9
10°	1118.9
12.5°	1038.6
15°	928.5
17.5°	799.2
20°	661.9
22.5°	529.3
25°	409.6
27.5°	306.8
30°	223.3
32.5°	159.8
35°	112.5
37.5°	79.5
40°	56.2
42.5°	41.0
45°	29.7
47.5°	21.7
50°	16.9
52.5°	12.9
55°	10.4
57.5°	8.0
60°	6.4
62.5°	4.8
65°	4.0
67.5°	3.2
70°	2.4
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)