

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219699

Luminaire Tested: **MRZ-1-REC-X-1H-L35-80-FL-UNV-X-STD**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219699
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14875)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-1H-L35-80-FL-UNV-X-STD
Description: MRZ INTEGRAL LED DOWNLIGHT
40 DEGREE FLOOD OPTIC, LIGHT LEVEL 1
Light Source: (1) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 704.9 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 6.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219699

CATALOG NUMBER: MRZ-1-REC-X-1H-L35-80-FL-UNV-X-STD

Luminous Intensity Polar Plot





TEST NUMBER: P219699

CATALOG NUMBER: MRZ-1-REC-X-1H-L35-80-FL-UNV-X-STD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87	84	82	81
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83	80	78	77
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77	73	71	69
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74	70	67	66
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71	67	64	63
10	79	71	66	62	78	70	65	62	69	65	62		69	65	62		68	64	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	636460
5°	648846
10°	628142
15°	535404
20°	382074
25°	234793
30°	126760
35°	60953
40°	29498
45°	15699
50°	9211
55°	6193
60°	3947
65°	2802
70°	2308
75°	1525
80°	2273
85°	0



TEST NUMBER: P219699

CATALOG NUMBER: MRZ-1-REC-X-1H-L35-80-FL-UNV-X-STD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.5	17.5
10°-20°	282.6	40.1
20°-30°	200.4	28.4
30°-40°	69.2	9.8
40°-50°	18.8	2.7
50°-60°	6.6	0.9
60°-70°	2.7	0.4
70°-80°	1.2	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	606.5	86.0
0°-40°	675.6	95.8
0°-60°	701.0	99.4
0°-90°	704.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	704.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1290	
5°	1310	124
15°	1048	283
25°	431	200
35°	101	69
45°	22	19
55°	7	7
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P219699

CATALOG NUMBER: MRZ-1-REC-X-1H-L35-80-FL-UNV-X-STD

CANDELA DISTRIBUTION (FULL):

	0°
0°	1290.0
2.5°	1295.6
5°	1310.1
7.5°	1306.1
10°	1253.8
12.5°	1167.9
15°	1048.2
17.5°	890.0
20°	727.7
22.5°	571.9
25°	431.3
27.5°	313.3
30°	222.5
32.5°	151.0
35°	101.2
37.5°	67.5
40°	45.8
42.5°	31.3
45°	22.5
47.5°	16.1
50°	12.0
52.5°	8.8
55°	7.2
57.5°	5.6
60°	4.0
62.5°	3.2
65°	2.4
67.5°	2.4
70°	1.6
72.5°	1.6
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)